



Specification
IN2101 & IN2102
Insulation Tester



ELECTRICAL

All specified accuracies are at 23°C ± 5°C, <80% RH for 1 year.

Temperature coefficient:

Add 0.1 x (specified accuracy) per °C (0°C to 18°C, 28°C to 40°C)

All accuracies below are expressed as ± (percentage of reading + digits)

Voltage

Range	Resolution	Accuracy
600V	1V	3% + 5

Voltage warning: >30V



Specification
IN2101 & IN2102
Insulation Tester

Insulation Resistance

IN2101					
Test voltage	Test current	Range	Operating range to BS EN 61557-2 (See note 1)	Resolution	Accuracy
500V	1mA at 0.5MΩ	4MΩ	0.1MΩ to 1000MΩ	0.001MΩ	3% + 5
		40MΩ		0.01MΩ	
		400MΩ		0.1MΩ	
		1000MΩ		1MΩ	

IN2102					
Test voltage	Test current	Range	Operating range to BS EN 61557-2 (See note 1)	Resolution	Accuracy
250V	1mA at 0.25 MΩ	4MΩ	0.1MΩ to 1000MΩ	0.001MΩ	3% + 5
		40MΩ		0.01MΩ	
		400MΩ		0.1MΩ	
		1000MΩ		1MΩ	
500V	1mA at 0.5MΩ	4MΩ	0.1MΩ to 4000MΩ	0.001MΩ	3% + 5
		40MΩ		0.01MΩ	
		400MΩ		0.1MΩ	
		4000MΩ		1MΩ	
1000V	1mA at 1MΩ	4MΩ	0.1MΩ to 5000MΩ	0.001MΩ	3% + 5
		40MΩ		0.01MΩ	
		400MΩ		0.1MΩ	
		5000MΩ		1MΩ	



Specification
IN2101 & IN2102
Insulation Tester

Test voltage accuracy: 0% to +20%

Short circuit test current: <1.5mA

Auto discharge: Discharge time <1s for C=1μF or less

Maximum capacitive load: Operable with up to 1μF load

Live circuit detection: >30V DC or AC rms, test is inhibited

Overload protection: 600V DC or AC rms

Continuity Resistance

Range	Open circuit test voltage	Short circuit test current	Operating range to BS EN 61557-4 (See note 1)	Resolution	Accuracy
40Ω	8V dc typical	≥ 200mA	0.2Ω to 40Ω	0.01Ω	3% + 5

Overload protection: 600V DC or AC rms

kΩ Resistance

Range	Open circuit test voltage	Short circuit test current	Resolution	Accuracy
1999kΩ	1.8V dc typical	0.37mA approx	≤999.9Ω - 0.1Ω ≥1000Ω - 1Ω	3% + 5

Overload protection: 600V DC or AC rms

●))) Resistance

Range	Open circuit test voltage	Short circuit test current	Resolution	Accuracy
999.9Ω	2V dc approx.	0.37mA approx.	0.1Ω	3% + 5

Overload protection: 600V DC or AC rms



Specification
IN2101 & IN2102
Insulation Tester

Note 1: The operating range where the operating uncertainty does not exceed ±30% in accordance with BS EN 61557-2 and BS EN 61557-4.

$$\text{Operating uncertainty (B)} = \pm (|A| + 1,15 \sqrt{E_2^2 + E_3^2})$$

where, A is the intrinsic uncertainty at reference conditions

E₂ is the variation due to supply voltage change

E₃ is the variation due to temperature change

GENERAL

Display: 5000 count liquid crystal display

Sample rate: 2.5 times/sec

Bar-graph: 51 segments

Overrange: (OL) is displayed

Power: 6 x 1.5V, AA alkaline batteries (IEC LR6, NEDA 15A)

Battery life (alkaline): >3000 measurements typical

Low battery indication:  symbol is displayed

Auto power off: After 5 minutes

Fuse: F 0.5 A/600 V 6.3x32mm fast blow ceramic

Dimensions: 90 x 210 x 54mm

Weight: Approx. 596g, including batteries

Includes: Carrying case, set of TL47 test leads, 6 x 1.5V AA batteries, instructions

ENVIRONMENTAL

Temperature & Humidity

(Operating): 0°C to 40°C <70% R.H.

(Storage): -20°C to 60°C < 80% R.H., batteries removed

Altitude: up to 2000m

Pollution degree: 2

IP rating: IP44, not for use in wet conditions



Specification IN2101 & IN2102 Insulation Tester

FUNCTIONALITY

Conforms to BS EN 61557-2 and BS EN 61557-4

SAFETY

Conforms to BS EN 61010-1, CAT III 600V
Class II, double insulation

EMC

Conforms to BS EN 61326-2-2

SPECIFICATION FOR TL47 TEST LEADS

Maximum voltage: 1000V AC/DC
Maximum current: 10A continuous
Connector: 4mm banana plug with fixed shroud

Environmental

Temperature (Operating & Storage): 0°C to 40°C
Altitude: up to 2000m
Pollution degree 2

Safety

Conforms to BS EN 61010-031, CAT IV 600V, CAT III 1000V, 10A (Probe tip covers fitted)
CAT II 1000V, 10A (Probe tip covers removed)
Class II, double insulation

Check out what else you can get from Martindale:

- 16th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Safe Isolation kits
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Imperial Park, Imperial Way,
Watford, Hertfordshire, WD24 4PP, UK
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk
© 2016 Martindale Electric Company Ltd.
Registered in England No. 3387451. Rev 7 LIT IN2101

