

M18 FTHCHS35-802

M18 FUEL™ TOP HANDLE CHAINSAW WITH 35 CM BAR

- Outstanding speed of cut in hardwood vs petrol or higher voltage top handle chainsaws
- High torque to complete cuts in demanding materials and maintains speed under heavy loads without bogging down
- FUEL™ technology to reach full throttle in under 1 second
- Up to 150 cuts in 10 x 10 cm cedar on a full M18™ HIGH OUTPUT™ 8.0 Ah battery charge for outstanding productivity
- Top handle design and optimised balance perfectly suited for arboricultural work
- Variable speed trigger allows for full control over the power curve
- Lanyard hang loop for quick attachment and removal from the harness
- Ergonomic angled bail handle for convenient handling in multiple positions
- Onboard scrench storage and easy access chain tensioner for improved user comfort
- All metal bucking spikes allow the user increased leverage when cutting
- No-spill oil reservoir with easy to access tank and clear viewing window
- Supplied with 76cc of oil, chain tool and bar cover
- The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Chain bar length (cm)	35
Chain speed (m/s)	15
Chain pitch ["]	8.3 / .325
Gauge ["]	1.1 / 0.043
Weight with battery pack (EPTA) (kg)	4.7 (M18 HB8)
Kit included	2 x M18 FB8 Battery packs, M12-18 FC Charger, No kitbox or bag supplied
Article number	4933499222