

# I.780+x | Cylindrical revolving handles

Technopolymer



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

## MATERIAL


Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

## STANDARD EXECUTIONS

- **I.780+x**: zinc-plated steel pin, hexagon socket at threaded end.
- **I.780+x-SST**: AISI 303 stainless steel pin, hexagonal socket at threaded end.



ELESA Original design



### I.780+x

Code	Description	D	L	d6g	d1	l	s	⚖️
124921	I.780/40+x-M6	18	40	M6	15	13	3	25
124931	I.780/50+x-M6	21	50	M6	17	13	3	37
124941	I.780/56+x-M6	22	56	M6	18	13	3	39
124951	I.780/65+x-M8	24.5	65	M8	20.5	15	4	66
124952	I.780/65+x-M10	24.5	65	M10	20.5	17	5	67
124961	I.780/80+x-M8	26.5	80	M8	21	15	4	76
124962	I.780/80+x-M10	26.5	80	M10	21	17	5	79
124971	I.780/90+x-M10	28.5	90	M10	22.5	20	5	90
124972	I.780/90+x-M12	28.5	90	M12	22.5	20	5	104
124981	I.780/100+x-M12	31	100	M12	25	20	5	115

### I.780+x-SST



Code	Description	D	L	d6g	d1	l	s	⚖️
124926	I.780/40+x-M6-SST	18	40	M6	15	13	3	25
124936	I.780/50+x-M6-SST	21	50	M6	17	13	3	37
124946	I.780/56+x-M6-SST	22	56	M6	18	13	3	39
124956	I.780/65+x-M8-SST	24.5	65	M8	20.5	15	4	66
124966	I.780/80+x-M8-SST	26.5	80	M8	21	15	4	76
124967	I.780/80+x-M10-SST	26.5	80	M10	21	17	5	79
124976	I.780/90+x-M10-SST	28.5	90	M10	22.5	20	5	90
124977	I.780/90+x-M12-SST	28.5	90	M12	22.5	20	5	104
124986	I.780/100+x-M12-SST	31	100	M12	25	20	5	115

Fixed & Revolving handles