



• Low Profile Shielded Plug

• High Performance Shielded Patch Cord

• Individually Packed With Test Results

Product Description

Copper patch cords are a critical component to ensuring the end to end performance of a network. HellermannTyton's patch cords are manufactured and tested to the highest quality to meet the component compliant requirements of the ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2 standards.

The patch cords incorporate a low profile shielded plug suitable for high density applications with an integral strain relief boot to minimise forces on the terminations and to manage the bend radius of the cable.

Features and Benefits

- High performance
- Low profile shielded plug - ideal for Data Centre applications, blade servers, etc.
- Manufactured and tested to meet component compliant requirements of ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2-1 Cat6 standard
- UK Manufactured
- Individually packed with test results
- Standard lengths: 1m, 2m, 3m, 5m, 10m
- Other lengths, colours and types available on request

| Product Description | Ordering Code | UNS Number |
|---|--------------------|----------------------|
| Shielded Copper Patch Cord Cat6 LSOH 0.5m | RJ45NGB-0.5MSLD/GY | Available on request |
| Shielded Copper Patch Cord Cat6 LSOH 1.0m | RJ45NGB-1.0MSLD/GY | Available on request |
| Shielded Copper Patch Cord Cat6 LSOH 2.0m | RJ45NGB-2.0MSLD/GY | Available on request |
| Shielded Copper Patch Cord Cat6 LSOH 3.0m | RJ45NGB-3.0MSLD/GY | Available on request |
| Shielded Copper Patch Cord Cat6 LSOH 5.0m | RJ45NGB-5.0MSLD/GY | Available on request |



Sales: 01604 707420
Website: www.htdata.co.uk

Test results



Connecting Hardware Test

Tested from: 1 MHz
 Tested to: 250 MHz
 Standard: ISO/IEC 11801 and
 ANSI/TIA/EIA 568-C.2-1
 Limits: Cat6 - Connector

Forward direction (A-B)



Reverse direction (B-A)



Tel: +44 (0) 1604 707420
 Web: www.htdata.co.uk
 Email: sales@htdata.co.uk