


Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KEIW17MPN
COUPLING HALF: Coupler
CONNECTION SIZE: G 3/8
FUNCTION: Self-Venting
BODY MATERIAL: Brass
CONNECTION TYPE: Female BSPP

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:

- General Industrial
- Industrial manufacturing equipment

Features/Benefits:

- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

MAXIMUM OPERATING TEMPERATURE	140 °F
LENGTH	57 mm
APPLICATION	Mobile & Defence
DIVISION	Low Pressure Connectors Europe Division
INTERCHANGE TYPE	European Profile
APPLICATION	Energy Management
PRODUCT TYPE	Pneumatic Quick Couplings
TECHNOLOGY	Pneumatics
PRODUCT STYLE	Quick-Connect
DIVISION	Low Pressure Connectors Europe Division
INDUSTRY	Transportation
COMPATIBLE FITTING	Series 25 Plug
FUNCTION	Self-Venting
OPERATION TYPE	Sleeve
BRAND	Parker
HEX SIZE	22 mm
QUANTITY PER BOX	5
FLOW RATE	830 L/min (air)
DIAMETER	7.4 mm (nominal)
INDUSTRY	General Industrial
CONNECTION TYPE	BSPP
VALVE INCLUDED	Yes
WEIGHT	0.11 kg
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
PRODUCT SERIES	Series 26

COUPLING HALF	Coupler
BODY MATERIAL	Brass
APPLICATION	Air & Gas Compressor
MINIMUM OPERATING TEMPERATURE	-20 °C
CONNECTION SIZE	G 3/8
SEAL MATERIAL	NBR
OUTSIDE DIAMETER	31 mm
PLATING TYPE	Nickel-Plated
APPLICATION	Electronics
MINIMUM OPERATING TEMPERATURE	-4 °F
BRAND	Rectus
REGION OF ORIGIN	Germany
SLEEVE MATERIAL	Brass
CONNECTION TYPE	Female
MAXIMUM OPERATING PRESSURE	174 psi
INDUSTRY	Electronics
VALVE TYPE	Standard Valve
APPLICATION	Trucks & Trailers
MAXIMUM OPERATING PRESSURE	12 bar
MAXIMUM OPERATING TEMPERATURE	60 °C