



EN ISO 20344:2011



ENDURANCE
CORVARA

81087-06L

S3 *CI SRC

Size: 36-48
Weight: 715 gr.

Fit: 11

Working Environment:
Building, Finishing-off building,
Farming and Gardening,
Multipurpose



FEATURES

UPPER

Greased Nubuk Dakar Leather
Hydro 1,8-2,0 mm
Full Grain Leather Hydro

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with anti-wear scaffold cap and high-comfort in-between insole. Outsole with self-cleaning tread pattern, with a formula designed to ensure greater grip. SRC Antislip standard.

TECHNOLOGIES

Removable Insole

337 climaction fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements

KX RESISTANT TO 3.0 mm. NAILS **fibercap sxt**

Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic control technology

Ergonomic rigid structure. It accommodates the heel, adjusting the foot support and control of the ankle in sideways movements. The plastic material increases protection of the ankle against sharp or pointy objects.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features

WED

Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUALMICRO DUALMICRO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)



		SOLE B1 PU - PU
SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE 1°) ≥0.28	0.52
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE 1°) ≥0.13	0.23 0.18

EN ISO 20344:2011