

WATERPROOF GT 58-23

Waterproof polypropylene tool trolley



General features

- waterproof and airtight (IP 67)
- interstackable
- corrosionproof, sandproof and dustproof
- shockproof and crushproof
- temperature rating -33°C/+90°C
- ergonomic handle, rubber coated grip
- jam free latches with user-friendly opening mechanism
- corrosion proof metal hinges with lid stay features
- manual pressure release valve (Art. PURGEVALVE.B)
- sealing O-ring (Art. NEOSEAL + item nr.)

Features

- document wallet in the lid
- 1 tool pallet with large elastic bands on both sides
- 1 tool pallet with FLEXI POUCHES™ on both sides
- bottom with layers of pre cubed foam
- 1 padlock with key included
- ergonomic central handle
- 2 side handles for two people carriage
- trolley with quick & safe lock/unlock telescopic handle
- padlockable in several points providing maximum security
- corrosion proof metal reinforced hinges
- positive stacking location

Versions

WATERPROOF GT 44-19 PEL
WATERPROOF GT 44-19 PSS
WATERPROOF GT 44-19 PTS
WATERPROOF GT 51-22 PEL
WATERPROOF GT 51-22 PTS
WATERPROOF GT 53-26 PEL
WATERPROOF GT 53-26 PTS
WATERPROOF GT 58-23

EAN

8024482174549



Technical features	A	B	C	D	E
mm internal dimensions	580	440	220	60	160
	Weight Kg 12,50				
inc internal dimensions	22 13/16	17 5/16	8 11/16	2 3/8	6 5/16
	Weight lbs 27.55				

