

ENGLISH

Product Datasheet

Equipment wire 3/24/0.07mm



8738867

Cross Section:



Characteristics: Relevant Standards: Operating Voltage: 250 V

Operating Temperature (°C): -40 to 105 °C

Applications:Extra-flexible wires, designed for connecting mobile assemblies

Construction:

Inner Conductor: Bare copper

Insulation: PVC Marking:No

Specification:

Conductor				Overall Diameter (mm)		Conductor resistance (Ω/Km, at 20°C)	Long term current Rating (A)
Size AWG	Area (mm2)	0/D (mm)	Stranding (mm)	Min.	Мах.	Max.	Max.
23	0.30	0.68	3/24/ 0.07	1.50	1.70	69.2	5.0

Product Range:

RS Code Description

8738863 Red equipment wire 3/24/0.07mm 100m 8738867 Green equipment wire 3/24/0.07mm 100m

RoHS√

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

Cross Section:



Characteristics: Relevant Standards: Operating Voltage: 250 V

Operating Temperature (°C): -40 to 105 °C

Applications:Extra-flexible wires, designed for connecting mobile assemblies

Construction:

Inner Conductor: Bare copper

Insulation: PVC Marking:No

Specification:

Conductor				Overall Diameter (mm)		Conductor resistance (Ω/Km, at 20°C)	Long term current Rating (A)
Size AWG	Area (mm2)	0/D (mm)	Stranding (mm)	Min.	Мах.	Мах.	Max.
23	0.30	0.68	3/24/ 0.07	1.50	1.70	69.2	5.0

Product Range:

RS Code Description

8738863 Red equipment wire 3/24/0.07mm 100m 8738867 Green equipment wire 3/24/0.07mm 100m