


TE Internal #: 293041-1  
Quick Disconnect Tab, 22 – 17 AWG, .32 – 1.04 mm<sup>2</sup> Wire, 6.35 mm  
[.25 in] Tab Width, Straight, Brass, Unplated Plating, Strip/Reel,  
FASTIN-FASTON 250

[View on TE.com >](#)



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**  
Wire Size: **.32 – 1.04 mm<sup>2</sup>**  
Mating Tab Width: **6.35 mm [ .25 in ]**  
Mating Tab Thickness: **.81 mm [ .032 in ]**

Features

Product Type Features

|                 |        |
|-----------------|--------|
| Insertion Force | Normal |
|-----------------|--------|

Configuration Features

|                                   |               |
|-----------------------------------|---------------|
| Compatible With Wire & Cable Type | Discrete Wire |
| Connection Capacity               | Single        |

Electrical Characteristics

|                |       |
|----------------|-------|
| Voltage Rating | 250 V |
|----------------|-------|

Contact Features

|                                |                 |
|--------------------------------|-----------------|
| Quick Disconnect Terminal Type | Tab             |
| Mating Tab Width               | 6.35 mm[.25 in] |
| Mating Tab Thickness           | .81 mm[.032 in] |
| Terminal Orientation           | Straight        |
| Contact Base Material          | Brass           |
| Terminal Plating Material      | Unplated        |
| Crimp Type                     | F-Crimp         |



Barrel Type

Open

Termination Features

|                       |              |
|-----------------------|--------------|
| Product Terminates To | Wire & Cable |
|-----------------------|--------------|

Mechanical Attachment

|                         |                |
|-------------------------|----------------|
| Locking Lance Height    | 1.5 mm[.06 in] |
| Wire Insulation Support | With           |
| Mating Retention Type   | Locking Lance  |

Dimensions

|                                      |                  |
|--------------------------------------|------------------|
| Product Length                       | 27 mm[1.063 in]  |
| Compatible Insulation Diameter Range | 2.31 mm[.091 in] |
| Terminal Material Thickness          | .36 mm[.014 in]  |
| Wire Size                            | .32 – 1.04 mm²   |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Insulation Option           | Uninsulated                |
| Operating Temperature Range | -40 – 110 °C[-40 – 230 °F] |

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Quantity | 3000       |
| Packaging Method   | Strip/Reel |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1241857-5  
5POS. FASTIN-FASTON\* TAB HSG, RAST5

TE Part # 2150035-2  
OCEAN\_2.0\_Applicator-E-080F130F-REA

TE Part # 7-2150035-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-080F130F

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(195)

Insertion & Extraction Tools(2)

Quick Disconnects(216)

Customers Also Bought

TE Part #926647-8  
UMNL CAP HSG. 15 POS

TE Part #2178301-1  
250 FASTON,F-SPR REC.,20-18 AWG, PNST

TE Part #1863007-1  
15P UMNL PLUG HSG

TE Part #1-1863005-2  
UMNL 12 WAY PLUG HOUSING





TE Part #1376384-1  
5mm B-T-W Conn. 4P HDR ASSEMBL

TE Part #1-1644055-2  
UMNL 6 WAY PLUG HOUSING

TE Part #1-1863006-2  
UMNL 12 WAY CAP HOUSING

TE Part #8-338069-2  
MICRO-MATCH SMD FTE

TE Part #1630372-1  
R5007 100R 10%

TE Part #1742543-4  
250 FASTON, FLAG, REC., 18-12 AWG, NPST

Documents

Product Drawings

FF 250 TAB 0.35-1.0MM2 BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_293041-1\_C\_c-293041-1-c.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_293041-1\_C\_c-293041-1-c.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_293041-1\_C\_c-293041-1-c.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

FASTIN-FASTON\* Connectors, 6.3 mm series TAB CONTACT.

Application Specification

Agency Approvals

UL Report

English