




COCKS & UNIONS



1832 GUNMETAL GLAND COCKS WITH HOSE UNION

Pressure/Temperature Rating

(Max Working)

10 bar at 120°C

Test Pressures (Hydraulic)

20 bar

Specification

Male parallel thread (BS 2779) x Hose Union.

Fitted with iron lever.

Size Range

| | $\frac{1}{2}$ | $\frac{3}{4}$ | 1 |
|------|---------------|---------------|---|
| 1832 | O | O | O |

Suitable for

| Steam | Water | Oil | Air | Gases |
|-------|-------|-----|-----|-------|
| | O | O | | |

Dimensions

| Nominal Size | | $\frac{1}{2}$ | $\frac{3}{4}$ | 1 |
|--------------------------|----|---------------|---------------|------|
| Hexagon Face to Pipe End | mm | 80 | 101 | 125 |
| Square Head | mm | 10.3 | 13.5 | 15.9 |
| Weight Approx. | kg | 0.36 | 0.65 | 1.12 |

1003 TEST/GAUGE COCKS

Used on pressure vessels, boilers, oil and water lines for connecting ancillary controls and taking samples.

Specification

Working pressure 7 bar at 100°C.

Hydraulically tested to 14 bar.

Gunmetal body. Round barrel.

Lever handle (in line with body when open).

Cannon nose.

Size Range

| | $\frac{1}{8}$ | $\frac{1}{4}$ | $\frac{3}{8}$ | $\frac{1}{2}$ | $\frac{3}{4}$ |
|------|---------------|---------------|---------------|---------------|---------------|
| 1003 | O | O | O | O | O |

Suitable for

| Steam | Water | Oil | Air | Gases |
|-------|-------|-----|-----|-------|
| | O | O | | |

Dimensions

| Nominal Size | | $\frac{1}{8}$ | $\frac{1}{4}$ | $\frac{3}{8}$ | $\frac{1}{2}$ | $\frac{3}{4}$ |
|----------------|----|---------------|---------------|---------------|---------------|---------------|
| Bore Diameter | mm | 4.0 | 5.0 | 6.0 | 8.0 | 13 x 10 |
| Weight Approx. | kg | 0.10 | 0.12 | 0.17 | 0.22 | 0.42 |

1004 TEST/GAUGE COCKS

Used on pressure vessels, boilers, oil and water lines for connecting ancillary controls and taking samples.

Specification

Working pressure 7 bar at 100°C.

Hydraulically tested to 14 bar.

Gunmetal round barrel.

Lever handle (in line with body when open).

Bent nose.

Size Range

| | $\frac{1}{8}$ | $\frac{1}{4}$ | $\frac{3}{8}$ | $\frac{1}{2}$ | $\frac{3}{4}$ |
|------|---------------|---------------|---------------|---------------|---------------|
| 1004 | O | O | O | O | O |

Suitable for

| Steam | Water | Oil | Air | Gases |
|-------|-------|-----|-----|-------|
| | O | O | | |

Dimensions

| Nominal Size | | $\frac{1}{8}$ | $\frac{1}{4}$ | $\frac{3}{8}$ | $\frac{1}{2}$ | $\frac{3}{4}$ |
|----------------|----|---------------|---------------|---------------|---------------|---------------|
| Bore Diameter | mm | 4.0 | 5.0 | 6.0 | 8.0 | 13 x 10 |
| Weight Approx. | kg | 0.11 | 0.14 | 0.18 | 0.25 | 0.45 |