


10044403-101LF - Minitek™ : Crimp-to-Wire Contact



www.fci.com

Specifications

Approvals / Certifications	
Approvals / Certifications	UL and CSA Approved
Mechanical	
Durability (Mating cycles)	100
Dimensional	
Size (Wire)	22 AWG to 24 AWG
Electrical	
Withstanding Voltage	650V rms
Current rating	2 amp Continuous
Resistance (Contact)	20 m ohms max.
Resistance (Insulation)	1000 M ohms min
Voltage rating	200V AC/DC
General	
Product Type	Crimp-to-Wire Contact
Mating half	Mates with 0.5 (0.02 in.) Square Pin. Mating Pin Length of 2.4 to 3.3 mm (0.094 to 0.13 in.) for Discrete Applications.
Other Features	
Packaging (Type)	Reel
Physical	
Material (Contact)	Phosphor Bronze
Plating (Contact area)	0.76 μ m (30 μ in.) Gold
Underplating (Contact)	1.27 μ m (50 μ in.) Nickel
Temperature (Operating - range)	-40°C to +105°C