

CRGV2512F100K

✓ ACTIVE

Neohm | Neohm CRGV

TE Internal #: 2-1879539-9

100K ohm, Surface Mount High Value/High Voltage Resistor, Thick Film, 2512, 1 W, 1 %, ±200 ppm/°C, Solder, 2 Terminations, Neohm CRGV

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 100K Ω

Resistor Type: High Value/High Voltage Resistor

Element Type: Thick Film

Package Size Code: 2512

Power Rating: 1 W

Features

Product Type Features

Resistor Type	High Value/High Voltage Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Resistance Value	100K Ω
Power Rating	1 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	6.35 mm[.25 in]
Product Width	3.2 mm[.126 in]



Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-1879530-4 CRGV1206 5% 2M4 1000V	 TE Part # 4-1879537-3 CRGV2010 1% 1M5 3000V	 TE Part # 2-1879532-0 CRGV2512 5% 330K 1600V	 TE Part # 2-1879537-6 CRGV2010 1% 1M0 3000V
--	--	---	--



Also in the Series | [Neohm CRGV](#)



Customers Also Bought



Documents

[Product Drawings](#)

[CRGV2512 1% 100K 1600V](#)

English

[CAD Files](#)

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1879539-9_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1879539-9_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1879539-9_BA.3d_stp.zip](#)

CRGV2512F100K

100K ohm, Surface Mount High Value/High Voltage Resistor, Thick Film, 2512, 1 W, 1 %, ±200 ppm/°C, Solder, 2 Terminations, Neohm CRGV



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
1309350_PASSIVE_COMPONENT

English

High Voltage Thick Film Chip Resistors - Type CRGV series

English