

UFW6-73B717ZZZ

UFW

FORK SENSORS





Ordering information

Туре	Part no.
UFW6-73B717ZZZ	6086481

Other models and accessories → www.sick.com/UFW

Illustration may differ



Detailed technical data

Features

Functional principle	Ultrasonic detection principle
Dimensions (W x H x D)	23.5 mm x 97 mm x 97.5 mm
Housing design	Fork shaped
Fork width	60 mm
Fork depth	73 mm
Detection area	40 mm
Repeatability	± 0.1 mm
Resolution	0.01 mm
Adjustment	Teach-in button, cable (One Point Adjustment, Two Point Adjustment, analog output: current/voltage, rising/falling)
Teach-in mode	One Point Adjustment Two Point Adjustment

Mechanics/electronics

Supply voltage	20 V DC 30 V DC ¹⁾
Ripple	< 10 % ²⁾
Current consumption	60 mA ³⁾
Ultrasonic frequency	170 kHz

 $^{^{1)}}$ Reverse polarity protected.

 $^{^{2)}}$ May not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.

 $^{^{4)}}$ Reference voltage DC 50 V.

Response time	6 ms
Switching output	Push-pull: PNP/NPN
Switching output (voltage)	Push-pull: PNP/NPN High = U_V - < 3 V/Low: \leq 3 V
Output current I _{max.}	100 mA
Initialization time	< 300 ms
Connection type	Male connector M12, 5-pin
Protection class	III ⁴⁾
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP67
Weight	Approx. 280 g
Housing material	Zinc diecast PBT
Sensing face material	Ultrasonic transducer: polyurethane foam, glass epoxy resin
Indication	LED green: Material edge aligned with the material positioning marking LED yellow: Material edge not aligned with the material positioning marking or outside detection area

¹⁾ Reverse polarity protected.

Communication interface

IO-Link	√ , V1.1
Data transmission rate	COM3 (230,4 kBaud)
Cycle time	4 ms
VendorID	26
DeviceID HEX	8389480
DeviceID DEC	0x800368
Process data length	32 Bit
Process data structure A	Bit 0 = switching signal Q_{L1} Bit 1 7 = empty Bit 8 15 = Skala Bit 16 31 = measured value
Analog output	Q_{A}
Number	1
Туре	Current output / voltage output
Current	4 mA 20 mA
Voltage	0 V 10 V
Digital output	Q_1
Number	1

Ambient data

Ambient operating temperature	+5 °C +60 °C
Ambient temperature, storage	-40 °C +85 °C

 $^{^{1)}}$ The sensor complies with the Electromagnetic compatibility (EMC) for the industrial sector (Radio Safety Class A).

²⁾ May not exceed or fall below U_V tolerances.

³⁾ Without load.

⁴⁾ Reference voltage DC 50 V.

Shock load	According to EN 60068-2-27
EMC	EN 60947-5-2 ¹⁾
UL File No.	NRKH.E191603 & NRKH7.E191603

¹⁾ The sensor complies with the Electromagnetic compatibility (EMC) for the industrial sector (Radio Safety Class A).


Classifications


ECLASS 5.0	27270909
ECLASS 5.1.4	27270909
ECLASS 6.0	27270909
ECLASS 6.2	27270909
ECLASS 7.0	27270909
ECLASS 8.0	27270909
ECLASS 8.1	27270909
ECLASS 9.0	27270909
ECLASS 10.0	27270909
ECLASS 11.0	27270909
ECLASS 12.0	27270909
ETIM 5.0	EC002720
ETIM 6.0	EC002720
ETIM 7.0	EC002720
ETIM 8.0	EC002720
UNSPSC 16.0901	39121528


Connection type/pinouts

Connection type	Male connector M12, 5-pin
Pinouts	
BN 1	+ (L+)
WH 2	$Q_{\rm A}$
BU 3	- (M)
BK 4	Q/C
GY 5	MF

Dimensional drawing (Dimensions in mm (inch))








- ① Fork width
- ② Fork depth
- ③ Detection axis
- ④ Male connector M12, 5-pin
- ⑤ Fixing hole
- ⑤ Display and adjustment elements

Pinouts


Pinouts, see technical data: Connection type/pinouts



Male connector, M12, 5-pin, A-coded

Adjustments

Display and adjustment elements



- ① Teach-in button
- ② LEDs (status display)

Recommended accessories

Other models and accessories → www.sick.com/UFW

	Brief description	Туре	Part no.
Connection n	nodules		
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A	IOLA2US-01101 (SiLink2 Master)	1061790
To the second	 Connection type head A: Male connector, M12, 4-pin, A-coded Connection type head B: Female connector, M12, 4-pin, A-coded Connection type head C: Female connector, M12, 4-pin, A-coded Signal type: Sensor/actuator cable Cable: 0.11 m, PVC Description: Sensor/actuator cable, Y-Junction, 2 x female connector M12, 4-pin, straight, 0.11 m PVC-cable, 1 x male connector M12, 4-pin, straight, to connect SICK Sensors with SICK Smart Sensors Note: T-coupler 2 x M12 female + M12 male straight with cable 	SYL-1204-G0M11-X1	6055011
	Connection type head A: Female connector, M12, 5-pin, straight, A-coded Description: Unshielded, Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm²	DOS-1205-G	6009719
	 Connection type head A: Male connector, M12, 5-pin, straight, A-coded Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Note: For field bus technology 	STE-1205-G	6022083
	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 050VB5XLEAX	2096240
Sensor Integr	ration Gateway		
Hansale II.	 Further functions: Web server integrated, IloT interface available (dual talk) Logic editor: no Communication interface: IO-Link, Ethernet, PROFINET, REST API, MQTT, OPC UA Product category: IO-Link Master 	SIG350-0004AP100	6076871
	 Further functions: Web server integrated, IIoT interface available (dual talk) Logic editor: no Communication interface: IO-Link, Ethernet, EtherNet/IP™, REST API, MQTT, OPC UA Product category: IO-Link Master 	SIG350-0005AP100	6076923

Brief description	Туре	Part no.
 Further functions: Web server integrated, IIoT interface available (dual talk) Logic editor: no 	SIG350-0006AP100	6076924
 Communication interface: IO-Link, Ethernet, EtherCAT[®], REST API, MQTT, OPC UA Product category: IO-Link Master 		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

