

Description

STAINLESS STEEL TOP PLATE CASTOR, RED POLYURETHANE 150MM

Fixed

KF4BA150-28L

Part Number

Swivel


KP4BA150-28L

Swivel and brake

KP4BD150-28L



| | Fixed | Swivel | Swivel+brake |
|--------------------------|----------------|---------|--------------|
| Wheel Diameter ØD | 150 mm | | |
| Overall Height H | 183 mm ±1 | | |
| Size of plate A X B | 105 x 85 mm±1 | | |
| Plate hole centres a x b | 80 x 60 mm±0,3 | | |
| Plate hole | 9 mm | | |
| Offset F ±1 | \ | 45 mm | 45 mm |
| Width of Tread | 40 mm±0,5 | | |
| Hardness of tread | shore A ± 98 | | |
| Load capacity | 180 Kg | | |
| Weight | 0,80 kg | 1,03 kg | 1,25 kg |
| Temperature | - 20 / + 60 °C | | |



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of White Polyamide.
Tread : Red injected Polyurethane non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Lightweight, highly resistant to knocks and other impacts, abrasion as well as a great many chemical substances.
Corrosion resistant, easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining red tyre.
Medium duty.