



SAFETY DATA SHEET
SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 1

Revision date: 05/02/2016

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SAPPHIRE AUTOLUBE COMPLETE / REFILL

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Lubricating Grease

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements: This product has no label elements.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

[cont...]

SAFETY DATA SHEET

SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 2

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	50-70%

MINERAL OIL (NOTE L - LESS THAN 3% DMSO EXTRACT)

265-090-8	64741-88-4	Substance with a Community workplace exposure limit.	-	20-50%
-----------	------------	--	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

[cont...]

SAFETY DATA SHEET
SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 3

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Wash the spillage site with large amounts of water.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Not applicable.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	-	5 mg/m3	-	-

MINERAL OIL (NOTE L - LESS THAN 3% DMSO EXTRACT)

UK	5mg/m3	10mg/m3	-	-
----	--------	---------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure all engineering measures mentioned in section 7 of SDS are in place.

Respiratory protection: Not applicable.

Hand protection: Gloves (oil-resistant). Nitrile gloves.

Eye protection: Safety glasses.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET

SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 4

9.1. Information on basic physical and chemical properties

State: Paste
Colour: Brown
Odour: Odourless
Evaporation rate: Negligible
Oxidising: Non-oxidising (by EC criteria)
Solubility in water: Insoluble
Viscosity: Highly viscous
Boiling point/range°C: No data available. **Melting point/range°C:** > 230
Flammability limits %: lower: No data available. **upper:** No data available.
Flash point°C: > 200 **Part.coeff. n-octanol/water:** No data available.
Autoflammability°C: > 200 **Vapour pressure:** No data available.
Relative density: < 1 **pH:** No data available.
VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

[cont...]

SAFETY DATA SHEET
SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 5

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: No data available

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

[cont...]

SAFETY DATA SHEET
SAPPHIRE AUTOLUBE COMPLETE / REFILL

Page: 6

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.