



Connectors > Contacts > Connector Contacts > Sig GRACE INERTIA Receptacle



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold (Au)**
Operating Voltage: **50 VDC**
Contact Retention Within Housing: **With**

[All Sig GRACE INERTIA Receptacle \(8\)](#)

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Insulation Resistance	1000 MΩ
Operating Voltage	50 VDC

Contact Features

Contact Underplating Material	Nickel
Mating Tab Thickness	.46 mm[.018 in]
Mating Tab Width	.5 mm[.02 in]
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	2.5 A



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
---------------------------------------	---------------

Dimensions

Compatible Insulation Diameter Range	1.09 – 1.9 mm[.043 – .075 in]
Wire Size	.079 – .38 mm²

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Reel
Packaging Quantity	6000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2151127-2 OCEAN_2.0_APPLICATOR-S-046F070FA	 TE Part # 1747066-3 GRACE INERTIA CONN 2.5 PLUG HSG 3P NATUR	 TE Part # 1-1747066-2 GRACE INERTIA CONN 2.5 PLUG HSG 2P RED	 TE Part # 2134384-1 GIC 2.5 REC CONT TIN PLATE TYPE (2L TYPE
 TE Part # 1747066-5 GRACE INERTIA CONN 2.5 PLUG HSG 5P NATUR	 TE Part # 2151127-1 OCEAN_2.0_APPLICATOR-S-046F070F-RSM	 TE Part # 1747066-8 GRACE INERTIA CONN 2.5 PLUG HSG 8P NATUR	 TE Part # 2-1747066-3 GRACE INERTIA CONN 2.5 PLUG HSG 3P BLUE
 TE Part # 7-2151127-7 OCEAN_2.0_SPARE_PART_KIT-046F070F	 TE Part # 1762236-1 SDE SAHT GIC 2.5 REC M 28-22 ASSY	 TE Part # 2-1747066-6 GRACE INERTIA CONN 2.5 PLUG HSG 6P BLUE	 TE Part # 1747066-2 GRACE INERTIA CONN 2.5 PLUG HSG 2P NATUR
 TE Part # 1747066-6 GRACE INERTIA CONN 2.5 PLUG HSG 6P NATUR	 TE Part # 1-1747066-5 GRACE INERTIA CONN 2.5 PLUG HSG 5P RED	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 1-1747066-6 GRACE INERTIA CONN 2.5 PLUG HSG 6P RED



Also in the Series | GRACE INERTIA 2.5




Connector Contacts(6)



Connector Hardware(7)




PCB Headers & Receptacles(173)



Power Contacts(2)



Rectangular Power Connectors(11)



Wire-to-Board Connector Assemblies & Housings(36)



Wire-to-Board Headers & Receptacles (173)


Customers Also Bought



TE Part #1969442-6
EP 2.5 TPA Housing, 6 Pos




TE Part #2-353046-2
DYNAMIC D-5200S TAB HSG 2P K/Y




TE Part #353255-1
110 HSG. PL EX REC. 7.6mm 3P NAT



TE Part #316292-5
3.2 CLUSTER REC L-TYPE TIN



TE Part #316294-1
3.2 CLUSTER REC S-TYPE



TE Part #353255-7
110 HSG. PL EX REC. 7.6mm 3P RED



TE Part #1742977-1
250FAST FLG RCPT AMVAR TPBR
CMA1500-4220



TE Part #1-1747066-2
GRACE INERTIA CONN 2.5 PLUG
HSG 2P RED



TE Part #1742881-1
250 FAST FLG RCPT AMVAR TPBR



TE Part #1747066-5
GRACE INERTIA CONN 2.5 PLUG
HSG 5P NATUR

Documents

Product Drawings

GRACE INERTIA CONN 2.5 REC CON

Japanese

CAD Files

Customer View Model

ENG_CVM_CVM_1747063-1_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1747063-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1747063-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English