



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XU8M18MA230W



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Diffuse with Background Suppression:

Diffuse:
Polarized Retroreflective:
Thru Beam:
Retroreflective:
Circuit Type:
Output Mode: Light Operate
Power: AC/DC
Voltage Range: 24-240
Max Load: 200 mA
Max Switching Frequency : 25 Hz
Temp Range: -25° to 55° C (-13° to 131° F)
NEMA Type: 4X (indoor use only)
IP Rating: 67
Standards: UL, CE Rohs

Specification:

Sensor Type: Proximity Diffuse / Background Suppression
Description: Photoelectric, Proximity Diffuse / Background Suppression, 18 mm Barrel, 24-240
Body Style: Barrel
Diameter: mm
Housing Material: Metal - NPB
Face Material: PMMA
Adjustment: Yes
Cable Size: 2.0 m (6.6 ft)
Connector Type:
Special Features: