




The Timken Company
4500 Mt Pleasant St. NW
N. Canton, OH 44720
Phone: (234) 262-3000
E-Mail: CustomerCAD@timken.com • Web site: www.timken.com

Timken Part Number 18590 - 18520, Tapered Roller Bearings - TS (Tapered Single) Imperial

This is the most basic and most widely used type of tapered roller bearing. It consists of two main separable parts: the cone (inner ring) assembly and the cup (outer ring). It is typically mounted in opposing pairs on a shaft.



[Specifications](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

Specifications	
Series	18500
Cone Part Number	18590
Cup Part Number	18520
Design Units	Imperial
Bearing Weight	0.60 lb 0.300 Kg
Cage Type	Stamped Steel

Dimensions	
d - Bore	1.6250 in 41.275 mm
D - Cup Outer Diameter	2.8750 in 73.025 mm

B - Cone Width	0.6875 in 17.463 mm
C - Cup Width	0.5000 in 12.700 mm
T - Bearing Width	0.6563 in 16.670 mm

Abutment and Fillet Dimensions

R - Cone Backface "To Clear" Radius¹	0.14 in 3.560 mm
r - Cup Backface "To Clear" Radius²	0.060 in 1.52 mm
da - Cone Frontface Backing Diameter	1.81 in 45.97 mm
db - Cone Backface Backing Diameter	2.09 in 53.09 mm
Da - Cup Frontface Backing Diameter	2.74 in 69.10 mm
Db - Cup Backface Backing Diameter	2.60 in 66.04 mm
Ab - Cage-Cone Frontface Clearance	0.08 in 2 mm
Aa - Cage-Cone Backface Clearance	-0.01 in -0.3 mm
a - Effective Center Location³	-0.11 in -2.80 mm

Basic Load Ratings

C90 - Dynamic Radial Rating (90 million revolutions)⁴	2960 lbf 13200 N
C1 - Dynamic Radial Rating (1 million revolutions)⁵	11400 lbf 50800 N
C0 - Static Radial Rating	13100 lbf 58100 N
C_{a90} - Dynamic Thrust Rating (90 million revolutions)⁶	1770 lbf 7890 N

Factors



K - Factor⁷	1.67
e - ISO Factor⁸	0.35
Y - ISO Factor⁹	1.71
G1 - Heat Generation Factor (Roller-Raceway)	21
G2 - Heat Generation Factor (Rib-Roller End)	15.4
Cg - Geometry Factor	0.0681

¹ These maximum fillet radii will be cleared by the bearing corners.

² These maximum fillet radii will be cleared by the bearing corners.

³ Negative value indicates effective center inside cone backface.

⁴ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values.


⁵ Based on 1×10^6 revolutions L_{10} life, for the ISO life calculation method.

⁶ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values for a single-row, $C_{90(2)}$ is the two-row radial value.

⁷ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁸ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁹ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.



IMPERIAL UNITS

ISO Factor - e 0.35
 ISO Factor - Y 1.71
 Bearing Weight 0.6 lb
 Number of Rollers Per Row 19
 Effective Center Location -0.11 inch

TIMKEN®

THE TIMKEN COMPANY
 NORTH CANTON, OHIO USA

18590 - 18520
 TS BEARING ASSEMBLY

K Factor 1.67
 Dynamic Radial Rating - C90 2960 lbf
 Dynamic Thrust Rating - Ca90 1770 lbf
 Static Radial Rating - C0 13100 lbf
 Dynamic Radial Rating - C1 11400 lbf

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

FOR DISCUSSION ONLY