



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	E cm	L cm	z cm
32102	12	15	2.5	8	3
32103	15	18	2.5	8	3
32104	20	22	2.5	8.4	3.4
32105	25	28	3	9.1	3.1

Art. no.	DN	d _g mm	E cm	L cm	z cm
32106	32	35	3	10.2	4.2
32107	40	42	4	12	4
32108	50	54	4	14	6
32109	65	76.1	6	23	11
32110	80	88.9	7	26	12
32111	100	108	8	31	15