

# Datasheet

**RS Stock No: 9129153**

## S-Type Impulse Sealer, 420mm Straight Bar



### Product Information

- Powder coated extruded aluminium
- Separate, electronic adjustment of sealing and cooling times
- 5mm sealing wire
- Sealing wire tension unit
- Gas spring controlled, electromagnetically locking sealing bar
- Manual or foot pedal actuation
- Integral safety cutting knife
- Usage guide: 200-400 seals per shift

### Product Data

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Seal length: 420mm</li><li>• Maximum film width/cutting length: 400mm</li><li>• Power consumption: 650W</li><li>• Dimensions of machine: 590 x 209 x 210mm</li><li>• Weight: 13kg</li><li>• Maximum film thickness: 10-500 micron</li><li>• Film types: LDPE, HDPE, PP, PVC, BOPP</li><li>• Sealing width: 5mm</li><li>• Power supply: 230V 50/60Hz</li></ul> | <ul style="list-style-type: none"><li>• Maximum heating wire temperature: 125°C</li><li>• Optimum environmental operating temperature: Between 5°C and 40°C</li><li>• Optimum environmental operating relative humidity: Between 30% and 90%</li><li>• Electric shock protection rating: First Class</li><li>• IP code: IP20</li><li>• Carton dimensions: 650 x 260 x 230mm</li><li>• Packed weight: 14.2kg</li></ul> |
|---|---|