



Main

Range	Acti9
Product or component type	Add-on residual current devices
Device short name	Vigi iC40
Range compatibility	Acti9 iC40
Poles description	1P + N
Neutral position	Left
[In] rated current	25 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
Product certifications	CE
Quality labels	IMQ OVE

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	400 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 61009-2-1
Local signalling	Fault indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

9 mm pitches	2
Height	95 mm
Width	36 mm
Depth	74 mm
Net weight	90 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminal bottom 1...16 mm ² rigid Tunnel type terminal bottom 1...10 mm ² flexible
Wire stripping length	14 mm for bottom connection
Tightening torque	2 N.m bottom

Environment

Standards	EN/IEC 61009-2-1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 61009-2-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Package 1 Weight	0.089 kg
Package 1 Height	0.420 dm
Package 1 width	0.820 dm
Package 1 Length	1.120 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins