

HCI-ET 70 W/830 SUPER 4Y

POWERBALL HCI-ET SUPER 4Y | Metal halide lamps with ceramic technology for enclosed luminaires



Areas of application

- Streets
- Outdoor lighting
- Industrial installations
- Exhibition halls and trade fairs
- Approved only for use in enclosed luminaires
- Outdoor applications only in suitable luminaires

Product benefits

- Up to 15 % higher lumen maintenance factor compared to HCI-ET standard lamps
- Up to 30 % higher lum. efficacy for lamps ≤ 100 W (comp. to NAV-T Super 4Y/6Y)
- Good color rendering
- Operation in existing HPS installations as ignition voltage of IEC 60662 is met
- Energy savings of up to 70 % when replacing inefficient mercury vapor lamps (HQL)
- Dimmable on conventional control gears and electronic control gears
- Optimum energy efficiency on POWERTRONIC PTo 3DIM ECGs
- UV values significantly below the maximum permitted thresholds to IEC 61167 thanks to UV filter

Product features

- White light due to POWERBALL ceramic technology
- Light color: warm white (830 WDL)
- Extended service lifetime: 4 years (at approx. 11 h/day)
- Very high luminous efficacy: up to 110 lm/W
- Lamp survival factor: 95 % after 16,000 hours burning time
- Average lifetime: up to 24,000 hours



Product datasheet

- ErP compliant according to EU Directive 245/2009

Technical data

Electrical data

Nominal wattage	70.00 W
Rated wattage	74.00 W
Lamp current	0.95000 A
PFC capacitor at 50 Hz	12 μ F ¹⁾
Nominal voltage	98 V
Ignition voltage	1.8 / 5.0 kVp ²⁾
Rated lamp efficacy (standard condition)	107 lm/W


¹⁾ At rated voltage and $\cos \varphi \geq 0.9$

²⁾ Minimum / Maximum

Photometrical data

Rated luminous flux	7900 lm
Color rendering index Ra	≥ 80
Color temperature	3000 K
Light color	830
Rated LLMF at 2,000 h	0.92
Rated LLMF at 4,000 h	0.90
Rated LLMF at 6,000 h	0.89
Rated LLMF at 8,000 h	0.88
Rated LLMF at 12,000 h	0.85
Rated LLMF at 16,000 h	0.83
Rated LLMF at 20,000 h	0.75
UV protection	Yes

Dimensions & weight



Diameter	71.0 mm
----------	---------

Product datasheet

Length	156.0 mm
Product weight	66.00 g

Temperatures

Maximum permitted outer bulb temperature	350 °C
Maximum permitted base edge temperature	210 °C

Lifespan

Rated lamp survival factor at 2,000 h	0.99
Rated lamp survival factor at 4,000 h	0.99
Rated lamp survival factor at 6,000 h	0.98
Rated lamp survival factor at 8,000 h	0.97
Rated lamp survival factor at 12,000 h	0.97
Rated lamp survival factor at 16,000 h	0.95
Rated lamp survival factor at 20,000 h	0.78
Lifespan B50	24000 h
Operation mode LLMF/LSF	50 Hz

Additional product data

New article	NEW
Base (standard designation)	E27
Design / version	Coated
System guarantee level	3 (2/5)
Lamp mercury content	6.7 mg

Capabilities

Dimmable	Yes ¹⁾
Burning position	Any
Enclosed luminaire required	Yes

¹⁾ In combination with POWERTRONIC PTo


Certificates & standards

Energy efficiency class	A+
Energy consumption	82 kWh/1000h

Country specific categorizations

ILCOS	ME/UB-70/830-H/E/SL-E27-71/156
-------	--------------------------------

Light Distribution



Spectral power distribution

System guarantee

For the vast majority of our lamps we are offering an extended system guarantee in conjunction with OSRAM POWERTRONIC control gear.




Guarantee


Product datasheet

Safety advice


Where possible, use a timer igniter (switch-off time of at least 15 minutes). Otherwise, switch off the luminaire for at least 15 minutes if a brief interruption has occurred to the mains voltage supply.



Circuit diagram



Circuit diagram



Circuit diagram

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899044753	HCI-ET 70 W/830 SUPER 4Y	Shipping carton box 24	360 mm x 285 mm x 355 mm	36.42 dm ³	2303.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For more information on the system guarantee and the terms and conditions of the guarantee visit

► www.osram.com/system-guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.