

CP0180A v 3.8 RS 850-962

SAFETY DATA SHEET

METAL LOADED EPOXY - RESIN

Page: 1

Compilation date: 20/09/2019

Revision No: 9

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: METAL LOADED EPOXY - RESIN

Product code: RS850-962

UFI No. JHN0-U0M7-C007-GCJM

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Epoxy resin preparation

1.3. Details of the supplier of the safety data sheet

Company name: RS Components Ltd

Birchington Road

Corby

Northamptonshire

NN17 9RS

England

Tel: +44 (0) 845 850 9900

Email: RCustomerServicesUK@rs-components.com

RS Components Ltd

Glenview Industrial Estate

Herberton Road

Rialto

Dublin 12

Tel No +353 (0) 1 415 3100

enquiries.ie@rs-components.com

1.4. Emergency telephone number

Emergency tel: +44 1865 407333 (24hr) +44 1235 239670 (24hr)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; -: EUH205

Most important adverse effects: Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. Toxic to aquatic life with long lasting effects. Contains epoxy constituents. May produce an allergic reaction.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

EUH205: Contains epoxy constituents. May produce an allergic reaction.

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental



[cont...]

SAFETY DATA SHEET

METAL LOADED EPOXY - RESIN

Page: 2

Signal words: Warning

Precautionary statements: P264: Wash hands thoroughly after handling.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P273: Avoid release to the environment.
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P321: Specific treatment (see information on this label)
P332+P313: If skin irritation occurs: Get medical advice/attention.

Haz. ingredients (label): BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}; BISPHENOL F

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT} - REACH registered number(s): 01-2119456619-26

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-033-5	25068-38-6	-	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Chronic 2: H411	30-50%

BARIUM SULFATE

-	7727-43-7	Substance with a Community workplace exposure limit.	-	10-30%
---	-----------	--	---	--------

LIMESTONE

215-279-6	1317-65-3	Substance with a Community workplace exposure limit.	-	10-30%
-----------	-----------	--	---	--------

TALC

238-877-9	14807-96-6	Substance with a Community workplace exposure limit.	-	2.9-10%
-----------	------------	--	---	---------

MAGNESIUM CARBONATE

208-915-9	546-93-0	Substance with a Community workplace exposure limit.	-	2.9-10%
-----------	----------	--	---	---------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Se i sintomi persistono consultare un medico.

[cont...]

SAFETY DATA SHEET

METAL LOADED EPOXY - RESIN

Page: 3

Ingestion: Do not induce vomiting. Wash out mouth with water. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. If unconscious and breathing is OK, place in the recovery position. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Do not attempt to take action without suitable protective clothing - see section 8 of SDS.
Evitare il contatto con la pelle e gli occhi.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - RESIN

Page: 4

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

BARIUM SULFATE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	-	4 g/m ³	-

LIMESTONE

UK	-	-	4 mg/m ³	-
----	---	---	---------------------	---

TALC

UK	-	-	1 mg/m ³	-
----	---	---	---------------------	---

MAGNESIUM CARBONATE

UK	-	-	4 mg/m ³	-
----	---	---	---------------------	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves. PVC gloves. Breakthrough time of the glove material > 1 hour.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: Ensure all engineering measures mentioned in section 7 of SDS are in place.

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - RESIN

Page: 5

9.1. Information on basic physical and chemical properties

State: Paste
Colour: Black
Odour: Not significant
Solubility in water: Insoluble
Viscosity: Viscous
Boiling point/range°C: > 200
Relative density: 1.80 +/-0.03
Flash point°C: Does not flash

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Polymerisation may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Acids. Bases. Amines.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes. In combustion emits toxic fumes of carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

ORL	MUS	LD50	15600	mg/kg
ORL	RAT	LD50	11400	mg/kg
SKN	RBT	LD50	>20	ml/kg

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - RESIN

Page: 6

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company. Waste disposal number - 08 04 12.

Waste code number: 08 04 12

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes. Waste disposal No. 15 01 08.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - RESIN

Page: 7

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(REACTION PRODUCTS OF EPICHLOROHYDRIN AND BISPENOL F)

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH205: Contains epoxy constituents. May produce an allergic reaction.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

CP0180B v3.8 RS 850-962

SAFETY DATA SHEET

METAL LOADED EPOXY - HARDENER

Page: 1

Compilation date: 20/09/2019

Revision No: 19

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier****Product name:** METAL LOADED EPOXY - HARDENER**Product code:** RS850-962**1.2. Relevant identified uses of the substance or mixture and uses advised against****Use of substance / mixture:** Epoxy hardener preparation**1.3. Details of the supplier of the safety data sheet****Company name:** RS Components Ltd

Birchington Road

Corby

Northamptonshire

NN17 9RS

England

Tel: +44 (0) 845 850 9900**Email:** RCustomerServicesUK@rs-components.com

RS Components Ltd

Glenview Industrial Estate

Herberton Road

Rialto

Dublin 12

Tel No +353 (0) 1 415 3100

enquiries.ie@rs-components.com**1.4. Emergency telephone number****Emergency tel:** +44 1865 407333 (24hr)

+44 1235 239670 (24hr)

Section 2: Hazards identification**2.1. Classification of the substance or mixture****Classification under CLP:** This product has no classification under CLP.**2.2. Label elements****Label elements:** This product has no label elements.**2.3. Other hazards****PBT:** This product is not identified as a PBT/vPvB substance.**Section 3: Composition/information on ingredients****3.2. Mixtures****Hazardous ingredients:**

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - HARDENER

Page: 2

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
202-013-9	90-72-2	-	Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315	1-2.9%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. If symptoms persist seek medical attention

Ingestion: Wash out mouth with water. Give 1 cup of water to drink every 10 minutes. Do not induce vomiting. Consult a doctor.

Inhalation: Move to fresh air in case of accidental inhalation of vapours. Get medical attention if discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - HARDENER

Page: 3

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Wash thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: Rubber gloves. PVC gloves. Breakthrough time of the glove material > 1 hour.

Eye protection: Safety glasses with side-shields. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: White

Odour: Sulphurus, Ammoniacal.

Solubility in water: Insoluble

Flash point°C: Does not flash

Vapour pressure: < 0.01 mmHg

Relative density: 1.73 - 1.79

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - HARDENER

Page: 4

9.2. Other information

Other information: Decomposition Temperature - >150 degC

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Flames. Hot surfaces. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Amines.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide. In combustion emits toxic fumes of sulphur oxides.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

ORL	RAT	LD50	1200	mg/kg
SKN	RAT	LD50	1280	mg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

[cont...]

SAFETY DATA SHEET
METAL LOADED EPOXY - HARDENER

Page: 5

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

12.4. Mobility in soil

Mobility: Insoluble in water. Heavier than water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 04 10

Disposal of packaging: Dispose of as normal industrial waste. Waste Code number 15 01 02.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

[final page]