




---

 PRODUCT-DETAILS

## AF2850T-30-11 230-240V 50/60Hz

### AF2850T-30-11 230-240V 50/60Hz Contactor




---

**General Information**

Extended Product Type	AF2850T-30-11 230-240V 50/60Hz
Product ID	1SFL687001R9101
EAN	7320500515433
Catalog Description	AF2850T-30-11 230-240V 50/60Hz Contactor
Long Description	The AF2850T-30-11 230-240V 50/60Hz is a 3 pole - 1000 V IEC or 1000 V UL contactor with pre-mounted auxiliary contacts and Main Circuit Bars, switching power circuits up to 2850 A (AC-1) or 2850 A UL general use. Thanks to the AF technology, the contactor has a wide control voltage range (230-240 V 50/60 Hz), managing large control voltage variations, reducing panel energy consumptions and ensuring distinct operations in unstable networks. Furthermore, surge protection is built-in, offering a compact solution. AF contactors have a block type design, can be easily extended with add-on auxiliary contact blocks and an additional wide range of accessories.

---

**Ordering**

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

## Popular Downloads

Data Sheet, Technical Information	1SBC100214C0202
Data Sheet, Technical Information (Part 2)	1SAC200017M0002
Instructions and Manuals	1SFC101050M0201
CAD Dimensional Drawing	2CDC001079B0201

## Dimensions

Product Net Width	438 mm
Product Net Depth / Length	244 mm
Product Net Height	422 mm
Product Net Weight	43 kg

## Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	2
Number of Auxiliary Contacts NC	2
Number of Poles	3P
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 60 Hz Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I <sub>th</sub> )	acc. to IEC 60947-4-1, Open Contactors $\Theta = 40^\circ\text{C}$ 2850 A
Rated Operational Current AC-1 (I <sub>e</sub> )	(1000 V) 40 °C 2850 A (1000 V) 55 °C 2600 A (1000 V) 70 °C 2300 A (690 V) 40 °C 2850 A (690 V) 55 °C 2600 A (690 V) 70 °C 2300 A
Rated Making Capacity AC-3	10 x I <sub>e</sub> AC-3
Rated Short-time Withstand Current Low Voltage (I <sub>cw</sub> )	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 3000 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 7500 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 12000 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 10000 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 5500 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 440 V 8400 A
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 1000 V acc. to UL/CSA 1000 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	8 kV Main Circuit 15 kV
Maximum Electrical Switching Frequency	(AC-1) 15 cycles per hour
Mechanical Durability	0.3 million

Maximum Mechanical Switching Frequency	60 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x Uc Min. ... 1.1 x Uc Max. (at $\theta \leq 70^\circ\text{C}$ )
Rated Control Circuit Voltage ( $U_c$ )	50 Hz 230 ... 240 V 60 Hz 230...240 V DC Operation 230 ... 240 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 48 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 48 V·A Holding at Max. Rated Control Circuit Voltage DC 20.5 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 2450 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 2540 V·A Pull-in at Max. Rated Control Circuit Voltage DC 2290 W
Power Loss	at Rated Operating Conditions per Pole 200 W
Operate Time	Between Coil De-energization and NC Contact Closing 35 ... 55 ms Between Coil De-energization and NO Contact Opening 35 ... 55 ms Between Coil Energization and NC Contact Opening 50 ... 80 ms Between Coil Energization and NO Contact Closing 50 ... 80 ms
Connecting Capacity Main Circuit	Bar 100 mm <sup>2</sup>
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup> Flexible 2x0.75 ... 2.5 mm <sup>2</sup> Solid 2 x 1 ... 4 mm <sup>2</sup> Stranded 2 x 1 .... 4 mm <sup>2</sup>
Connecting Capacity	Bar 100 mm <sup>2</sup>
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Connecting Terminals (delivered in open position) Main Poles	M 3.5 (+,-) pozidriv 2 screw with cable clamp
Recommended Screw Driver	Main Circuit M12 Control Circuit Pozidriv 2 Control Circuit M3.5
Tightening Torque	Cable Lug 45 N·m Main Circuit 45 N·m
Terminal Type	Screw Terminals
Suitable for Product Class	Block ContactorsBlock Contactors
Product Name	Block Contactor

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 1000 V
General Use Rating UL/CSA	(1000 V AC) 2850 A (600 V AC) 2850 A

## Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... 50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... 70 °C Close to Contactor for Storage -40 ... 70 °C Operation -40 ... 70 °C Storage -40 ... +70 °C
Maximum Operating Altitude Permissible	Without Derating 3000 m

## Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

### ABB EcoSolutions

End Of Life Disassembling Instructions	1SFC100112M0005
Environmental Product Declaration - EPD	1SFC100110D0201

### Certificates and Declarations

CB Certificate	SEMKO_SE70500M1
CQC Certificate	CQC2013010304604054
Declaration of Conformity - CCC	2020980304001265
Declaration of Conformity - CE	2CMT2019-005796
Declaration of Conformity - UKCA	2CMT2020-006118
EAC Certificate	9AKK107046A8618
UL Certificate	9AKK107046A8617

### Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	555 mm
Package Level 1 Depth / Length	365 mm
Package Level 1 Height	500 mm
Package Level 1 Gross Weight	45 kg
Package Level 1 EAN	7320500515433

### External Classifications and Standards

Object Classification Code	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors

## Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
1SFN076407R1000	LW1250 Terminal Enlargement	LW1250	1	piece
1SFN165503R9215	AF1250 Cover Replacement Part	Spare Part Cover AF1250	1	piece
1SFN165503R9245	AF1250 Base Replacement Part	Spare Part Bottom AF1250	1	piece
1SFN166403R1000	ZL1250 Main Contact Kit	ZL1250	1	piece
1SFN165503R9216	AF1350 Cover Replacement Part	Spare Part Cover AF1350	1	piece
1SFN165503R9250	AF1350 Base Replacement Part	Spare Part Bottom AF1350	1	piece
1SFN166503R1000	ZL1350 Main Contact Kit	ZL1350	1	piece
1SFN166503R1001	ZL1350-1 Main Contact Kit	ZL1350-1	1	piece
1SFN165503R9246	AF1350/1650 Base Replacement Part	Spare Part Bottom AF1350/AF1650	1	piece
1SFN165503R9218	AF1650 Cover Replacement Part	Spare Part Cover AF1650	1	piece
1SFN165503R9247	AF1650 Base Replacement Part	Spare Part Bottom AF1650	1	piece
1SFN165503R9251	AF1650 Base Replacement Part	Spare Part Bottom AF1650	1	piece
1SFN166510R1001	ZW1650 Arc Shute	ZW1650	1	piece
1SFN166521R1070	ZP1650-70 Circuit Board	ZP1650-70	1	piece
1SFN166703R1000	ZL1650 Main Contact Kit	ZL1650	1	piece
1SFN166703R1001	ZL1650-1 Main Contact Kit	ZL1650-1	1	piece
1SFN156570R7026	ZAF1650-70 100-250V AC/DC Operating Coil	ZAF1650-70	1	piece
1SFN165503R9219	AF1650T Cover Replacement Part	Spare Part Cover AF1650T	1	piece
1SFN165503R9126	T-Delay board Replacement Kit	T-Delay board	1	piece
1SFN165503R9223	AF2650T Cover Replacement Part	Spare Part Cover AF2650T	1	piece
1SFN165503R9211	AF400 Cover Replacement Part	Spare Part Cover AF400	1	piece
1SFN165703R1000	ZL400 Main Contact Kit	ZL400	1	piece

## Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors → AF Contactors → AF2850

