

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Universal, 5-position, Pin, straight, M12-SPEEDCON, coding: A, on free cable end, Rear mounting, M12 x 1, Individual wires, cable length: 0.6 m, 0.34 mm², TPE litz wire, potted, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238672

Commercial data

Item number	1402137
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	ABQ
Product key	ABQCGA
GTIN	4046356584906
Weight per piece (including packing)	31.8 g
Weight per piece (excluding packing)	21.8 g
Customs tariff number	85444290
Country of origin	DE

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
General	Contact connection method: Crimp connection
Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.

Safety note

Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
	• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	• The products are suitable for applications in plant, controller, and electrical device engineering.
	• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.
	• Assembled products may not be manipulated or improperly opened.
	• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
	• When using the product in direct connection with third-party manufacturers, the user is responsible.
	• For operating voltages > 50 V AC, conductive connector housings must be grounded
	• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
	• Observe the corresponding technical data. You will find information: <ul style="list-style-type: none">o On the producto On the packing labelo In the supplied documentationo Online at phoenixcontact.com/products under the product
	• Only use tools recommended by Phoenix Contact
	• Use a protective cap to protect connectors that are not in use.

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Mounting

Mounting type

Rear mounting M12 x 1

Product properties

Product type

Circular connectors (device side)

Sensor type

Universal

Number of positions

5

No. of cable outlets

1

Shielded

no

Coding

A

Thread type

M12

Insulation characteristics

Overvoltage category

II

Degree of pollution

3

Material specifications

Material Molding compound

PUR (potted)

Flammability rating according to UL 94

V0

Seal material

NBR

Contact material

CuZn

Contact surface material

Au

Contact carrier material

PA 6.6

Material for screw connection

Zinc die-cast, nickel-plated

Conductor material

Tin-plated Cu litz wires

Electrical properties

Contact resistance

≤ 3 mΩ

Insulation resistance

≥ 100 MΩ

Nominal voltage U_N

60 V

Nominal current I_N

4 A

Max. conductor resistance

57.6 mΩ/m

Connection data

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

Conductor connection

Connection method	Individual wires
Contact connection type	Pin
Conductor cross section	0.34 mm ²

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	0.6 m
Cable type	TPE litz wire
Signal type/category	Universal
Wire diameter incl. insulation	1.2 mm ±0.07 mm
Single wire, color	black, brown, blue, white, gray
Cable cross section	0.34 mm ²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Material wire insulation	TPE
Thickness, insulation	0.21 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 57.6 mΩ/m
Cable insulation resistance	≥ 20 MΩ*km

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-25 °C ... 90 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting

1402137

<https://www.phoenixcontact.com/in/products/1402137>


Drawings

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

Diagram




I = current strength, T = ambient temperature

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting

1402137

<https://www.phoenixcontact.com/in/products/1402137>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137
<https://www.phoenixcontact.com/in/products/1402137>

Classifications

ECLASS

ECLASS-13.0	27440103
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fbf30b9e-1745-4571-a3c4-c2a35541943a

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

Accessories

PROT-M12 FS - Sealing cap

1560251

<https://www.phoenixcontact.com/in/products/1560251>



M12 sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

PROT-M12 FS-M - Sealing cap

1430488

<https://www.phoenixcontact.com/in/products/1430488>



M12 metal sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

SACC-DSI-MS-5CON-M12/0,6 SCO - Device connector rear mounting



1402137

<https://www.phoenixcontact.com/in/products/1402137>

SACC-M12-SEAL - Flat gasket

1424275

<https://www.phoenixcontact.com/in/products/1424275>

M12 flat gasket, for M12 flush-type connectors for rear mounting



SACC-E-MU-M12 - Flat nut

1409362

<https://www.phoenixcontact.com/in/products/1409362>

Flat nut, Screw mounting, M12 x 1, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238816



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in