SIEMENS

Data sheet 3RH1911-1FA31



AUXILIARY SWITCH BLOCK, 31, 3NO+1NC, DIN EN50005, SCREW CONNECTION, F. CONTACTOR RELAYS A. CONTACT. FOR SWITCHING MOTORS, SIZE S00

General technical data:		
product brand name		SIRIUS
Suitability for use		Contactor relay and power contactor
Protection class IP on the front		IP20
Ambient temperature		
during storage	°C	-55 + 80
during operation	°C	-25 + 60
Mechanical service life (switching cycles) typical		10 000 000
Electrical endurance (switching cycles) at AC-15 at 230 V typical		200 000
Contact reliability		one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
Contact reliability of auxiliary contacts		1 faulty switching per 100 million (17 V, 1 mA)
Insulation voltage with degree of pollution 3 rated value	V	690
Surge voltage resistance rated value	kV	6

Auxiliary circuit:

Number of NC contacts for auxiliary contacts

• instantaneous contact

Number of NO contacts for auxiliary contacts		
• instantaneous contact		3
Operating current of auxiliary contacts at AC-12		
● at 24 V	Α	10
● at 230 V	Α	10
• maximum	Α	10
Operating current	_	
of auxiliary contacts		
— at AC-14		
— at 125 V	Α	6
— at 250 V	Α	6
— at AC-15		
— at 24 V	Α	6
— at 230 V	Α	6
— at 400 V	Α	3
• at AC-15 at 690 V rated value	Α	1
Operating current		
 with 2 current paths in series at DC-12 		
— at 24 V rated value	Α	10
— at 60 V rated value	Α	10
— at 110 V rated value	Α	4
— at 220 V rated value	Α	2
— at 440 V rated value	Α	1.3
— at 600 V rated value	Α	0.65
• with 3 current paths in series at DC-12		
— at 24 V rated value	Α	10
— at 60 V rated value	Α	10
— at 110 V rated value	Α	10
— at 220 V rated value	Α	3.6
— at 440 V rated value	Α	2.5
— at 600 V rated value	Α	1.8
Operating current		
 of auxiliary contacts at DC-13 		
— at 24 V	Α	6
— at 60 V	Α	2
— at 110 V	Α	1
— at 220 V	Α	0.3
• with 2 current paths in series at DC-13		
— at 24 V rated value	Α	10
— at 60 V rated value	Α	3.5
— at 110 V rated value	Α	1.3

— at 220 V rated value	Α	0.9
— at 440 V rated value	Α	0.2
— at 600 V rated value	Α	0.1
 with 3 current paths in series at DC-13 		
— at 24 V rated value	Α	10
— at 60 V rated value	Α	4.7
— at 110 V rated value	Α	3
— at 220 V rated value	Α	1.2
— at 440 V rated value	Α	0.5
— at 600 V rated value	Α	0.26

Installation/ mounting/ dimensions:			
Mounting type		snap-on mounting	
Width	mm	36.5	
Height	mm	37.5	
Depth	mm	41.5	

Connections/ Terminals:	
Type of electrical connection for auxiliary and control current circuit	screw-type terminals
Type of connectable conductor cross-sections	
• for auxiliary contacts	
— finely stranded	
 — with core end processing 	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
 at AWG conductors for auxiliary contacts 	2x (20 16), 2x (18 14)

Safety related data:	
Product function Mirror contact acc. to IEC 60947-4-1	Yes
• Note	with 3RT1
Product function positively driven operation acc. to IEC 60947-5-1	Yes
• Note	with 3RH1

Certificates/ approvals:

General Product Approval

Functional Safety/Safety of Machinery

Declaration of Conformity









Baumusterbescheini gung



Test	Shipping Approval		
Certificates			

spezielle Prüfbescheinigunge







GL





Shipping Approval	other			Railway	
	sonstig	Umweltbestätigung	Bestätigungen	Bestätigungen	



Umweltbestatigung

Bestatigungen

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/industrymall

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RH19111FA31

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RH19111FA31

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RH19111FA31&lang=en



