

# LC1D18ND

TeSys D contactor - 3P(3 NO) - AC-3 -  $\leq 440$   
V 18 A - 60 V DC coil



## Main

Range of product	TeSys D
Product or component type	Contacteur
Device short name	LC1D
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	$\leq 690$ V AC 25...400 Hz for power circuit $\leq 690$ V DC for power circuit
[Ie] rated operational current	18 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-3 for power circuit 32 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-1 for power circuit
Motor power kW	4 kW at 220...230 V AC 50/60 Hz 7.5 kW at 380...400 V AC 50/60 Hz 9 kW at 415...440 V AC 50/60 Hz 10 kW at 500 V AC 50/60 Hz 10 kW at 660...690 V AC 50/60 Hz
Motor power HP (according to UL / CSA)	1 hp at 115 V AC 50/60 Hz for 1 phase motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 10 hp at 460/480 V AC 50/60 Hz for 3 phases motors 15 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Control circuit type	DC standard
Control circuit voltage	60 V DC
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overtoltage category	III
[Ith] conventional free air thermal current	10 A at $\leq 60$ °C for signalling circuit 32 A at $\leq 60$ °C for power circuit
Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 300 A at 440 V for power circuit conforming to IEC 60947
Rated breaking capacity	300 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit 145 A $\leq 40$ °C 10 s power circuit 240 A $\leq 40$ °C 1 s power circuit 40 A $\leq 40$ °C 10 min power circuit 84 A $\leq 40$ °C 1 min power circuit

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 50 A gG at ≤ 690 V coordination type 1 for power circuit 35 A gG at ≤ 690 V coordination type 2 for power circuit
Average impedance	2.5 mOhm at 50 Hz - Ith 32 A for power circuit
[Ui] rated insulation voltage	690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL
Power dissipation per pole	2.5 W AC-1 0.8 W AC-3
Safety cover	With
Mounting support	Plate Rail
Standards	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 n°14
Product certifications	BV CCC CSA DNV GL GOST RINA UL LROS
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 1 cable(s) 1.5...6 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.5...6 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 1 cable(s) 1...6 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 1 cable(s) 1.5...6 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.5...6 mm <sup>2</sup> - cable stiffness: solid - without cable end
Tightening torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
Operating time	53.55...72.45 ms closing 16...24 ms opening

Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability (millions)	30 Mcycles
Operating rate	3600 cyc/h at $\leq 60\text{ }^{\circ}\text{C}$

## Complementary

Coil technology	Built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	0.1...0.25 $U_c$ at $60\text{ }^{\circ}\text{C}$ drop-out 0.7...1.25 $U_c$ at $60\text{ }^{\circ}\text{C}$ operational
Time constant	28 ms
Inrush power in W	5.4 W at $20\text{ }^{\circ}\text{C}$
Hold-in power consumption in W	5.4 W at $20\text{ }^{\circ}\text{C}$
Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non-overlap time	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm for signalling circuit

## Environment

IP degree of protection	IP2x front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	-5... $60\text{ }^{\circ}\text{C}$
Ambient air temperature for storage	-60... $80\text{ }^{\circ}\text{C}$
Permissible ambient air temperature around the device	-40... $70\text{ }^{\circ}\text{C}$ at $U_c$
Operating altitude	3000 m without derating in temperature
Fire resistance	$850\text{ }^{\circ}\text{C}$ conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms
Height	77 mm
Width	45 mm
Depth	95 mm
Product weight	0.49 kg