

Issue Date 04-May-2015

Revision Date 03-Dec-2015

Version 1

1. IDENTIFICATION

Product identifier

Product Name Dissipator 746

Other means of identification

Product Code MS-746

UN/ID no. None

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Adhesives.

Uses advised against None known

Details of the supplier of the safety data sheet

Manufacturer Address

Hernon Manufacturing Inc.
121 Tech Drive
Sanford, FL 32771
800-527-0004

Emergency telephone number

Company Phone Number 407-322-4000

Emergency Telephone Chemtel 800-255-3924

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Inhalation (Dusts/Mists)	Category 3
Serious eye damage/eye irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3

Label elements

Emergency Overview

Warning

Hazard statements

Causes serious eye irritation

Toxic if inhaled

May cause respiratory irritation. May cause drowsiness or dizziness

Harmful to aquatic life with long lasting effects

**Appearance** White**Physical state** Paste**Odor** Mild**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling
 Do not breathe dust/fume/gas/mist/vapors/spray
 Wear protective gloves/eye protection/face protection

Precautionary Statements - Response

Get medical advice/attention if you feel unwell
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 IF ON SKIN: Wash with plenty of water and soap
 If skin irritation occurs: Get medical advice/attention
 Take off contaminated clothing and wash it before reuse
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 IF INHALED: Call a POISON CENTER or doctor if you feel unwell

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Skin Contact: May cause allergic skin reaction
 Eye Contact: may cause moderate irritation, tearing or redness.

Other Information

Not applicable

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance

Chemical Name	CAS No.	Weight-%	Trade Secret
Alumina Trihydrate	21645-51-2	60-100	*
Tetrahydrofurfuryl methacrylate	2455-24-5	10-20	*
Elastomer	249347-78-8	5-10	*
Hydroxyalkyl Methacrylate	27813-02-1	5-10	*
Cumene Hydroperoxide	80-15-9	1-3	*
Saccharin	81-07-2	1-3	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures**Eye contact**

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids.
 Consult a physician.

Skin contact

Wash with soap and water. Flush skin with water for several minutes. Remove contaminated clothing and shoes. If irritation develops, seek medical attention. Wash clothing before reuse.

Inhalation	Remove to fresh air. If breathing is difficult, give oxygen. If breathing has stopped, give artificial respiration. Get medical attention immediately.
Ingestion	Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Call a POISON CENTER or doctor/physician if you feel unwell.

Most important symptoms and effects, both acute and delayed

Symptoms	Avoid prolonged contact with eyes, skin, and clothing.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES**Suitable extinguishing media**

Use CO₂, dry chemical, or foam.

Unsuitable extinguishing media None.

Specific hazards arising from the chemical

No information available.

Hazardous combustion products Carbon oxides. Nitrogen oxides (NO_x). Irritating organic vapors.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures**

Personal precautions	Use personal protective equipment as required. Ensure adequate ventilation, especially in confined areas.
-----------------------------	---

For emergency responders	Use personal protection recommended in Section 8.
---------------------------------	---

Environmental precautions

Environmental precautions	Do not allow into any sewer, on the ground or into any body of water. See Section 12 for additional ecological information.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
--------------------------------	--

Methods for cleaning up	Soak up with inert absorbent material. Store in a closed container until ready for disposal.
--------------------------------	--

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Avoid contact with skin, eyes or clothing. Avoid breathing vapors or mists. Wash thoroughly after handling. Ensure adequate ventilation, especially in confined areas.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep at temperatures between 7 and 29 °C.

Incompatible materials Strong oxidizers.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Alumina Trihydrate 21645-51-2	TWA: 1 mg/m ³ respirable fraction	-	-

Appropriate engineering controls

Engineering Controls Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing. Wear protective nitrile rubber gloves.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Paste	Odor	Mild
Appearance	No information available	Odor threshold	No information available
Color	White		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	Does not apply	
Melting point / freezing point	No information available	
Boiling point / boiling range	> 149 °C / 300 °F	
Flash point	> 93 °C / > 200 °F	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	Not available	
Lower flammability limit:	Not available	
Vapor pressure	< 5mm @ 80° F	

Vapor density	No information available
Relative density	1.60
Water solubility	slightly soluble
Solubility in other solvents	No information available
Partition coefficient	No information available
Autoignition temperature	No information available
Decomposition temperature	No information available
Kinematic viscosity	No information available
Dynamic viscosity	No information available
Explosive properties	No information available
Oxidizing properties	No information available

Other Information

Softening point	No information available
Molecular weight	No information available
VOC Content (%)	No information available
Density	No information available
Bulk density	No information available

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous polymerization	Hazardous polymerization does not occur.
---------------------------------	--

Conditions to avoid

Incompatible materials.

Incompatible materials

Strong oxidizers.

Hazardous Decomposition Products

Carbon oxides. Nitrogen oxides (NOx). Irritating organic vapors.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information**

Inhalation	May cause irritation of respiratory tract.
Eye contact	May cause irritation.
Skin contact	Substance may cause slight skin irritation.
Ingestion	Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Alumina Trihydrate 21645-51-2	> 5000 mg/kg (Rat)	-	-
Hydroxyalkyl Methacrylate 27813-02-1	= 11200 mg/kg (Rat)	> 3000 mg/kg (Rabbit)	-
Cumene Hydroperoxide 80-15-9	= 382 mg/kg (Rat)	= 0.126 mL/kg (Rabbit)	= 220 ppm (Rat) 4 h

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Germ cell mutagenicity No information available.

Carcinogenicity No information available.

Chemical Name	ACGIH	IARC	NTP	OSHA
Saccharin 81-07-2	-	Group 3	-	-

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Aspiration hazard No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document.

ATEmix (oral) 4,178.00 mg/kg

ATEmix (dermal) 22,222.00 mg/kg

ATEmix (inhalation-dust/mist) 25.00 mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

Harmful to aquatic life with long lasting effects

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Tetrahydrofurfuryl methacrylate 2455-24-5	-	31.1 - 38.8: 96 h Pimephales promelas mg/L LC50 flow-through	-
Hydroxyalkyl Methacrylate 27813-02-1	-	493: 48 h Leuciscus idus melanotus mg/L LC50 static	-
Cumene Hydroperoxide 80-15-9	-	3.9: 96 h Oncorhynchus mykiss mg/L LC50 static	7: 24 h Daphnia magna mg/L EC50
Saccharin 81-07-2	-	18300: 96 h Pimephales promelas mg/L LC50	-

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical Name	Partition coefficient
Hydroxyalkyl Methacrylate 27813-02-1	0.97

Other adverse effects No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

Chemical Name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Cumene Hydroperoxide 80-15-9	-	-	-	U096

Chemical Name	California Hazardous Waste Status
Cumene Hydroperoxide 80-15-9	Toxic Ignitable

14. TRANSPORT INFORMATION

DOT
 UN/ID no. Not regulated
 Proper shipping name None
 Hazard Class Not regulated
 Packing Group None
 Special Provisions None

IATA
 UN/ID no. Not regulated
 Proper shipping name None
 Hazard Class Not regulated
 Packing Group None
 Special Provisions None

IMDG
 UN/ID no. Not regulated
 Proper shipping name None
 Hazard Class Not regulated
 Packing Group None
 Special Provisions None

RID
 UN/ID no. Not regulated
 Proper shipping name None
 Hazard Class Not regulated
 Packing Group None
 Special Provisions None

ADR
 UN/ID no. Not regulated
 Proper shipping name None
 Hazard Class Not regulated
 Packing Group None
 Special Provisions None

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
 DSL/NDSL Complies
 EINECS/ELINCS Complies
 ENCS Complies
 IECSC Complies
 KECL Complies
 PICCS Complies

AICS Complies

All ingredients are on the inventory or are exempt from listing.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
Cumene Hydroperoxide - 80-15-9	1.0
Saccharin - 81-07-2	1.0

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Cumene Hydroperoxide 80-15-9	10 lb	-	RQ 10 lb final RQ RQ 4.54 kg final RQ

US State Regulations**California Proposition 65**

This product contains the following Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Cumene Hydroperoxide 80-15-9	X	X	X
Saccharin 81-07-2	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

16. OTHER INFORMATION, INCLUDING DATE OF PREPARATION OF THE LAST REVISION

NFPA	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties -
HMIS	Health hazards 2	Flammability 1	Physical hazards 1	Personal protection X

Prepared By SDS coordinator
Issue Date 04-May-2015
Revision Date 03-Dec-2015
Revision Note

No information available

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet