




Passive Components > Resistors > Through-Hole Resistors



Resistance Value: 470 Ω

Resistor Type: Power Resistor

Element Type: Ceramic Composition, Wire Wound

Power Rating: 5 W

Resistance Class: Up to 1kΩ

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Ceramic Composition, Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Resistance Value	470 Ω
Power Rating	5 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	25 x 8.5 mm
------------------------------	-------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±300 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

EP5W470RJ


470 ohm, Through-Hole Power Resistor, Ceramic Composition / Wire Wound, 5 W, 5 %, ±300 ppm/°C, Axial-Leaded, Copper Termination, 25 x 8.5 mm, Neohm EP




TE Part # 2176083-1
EP 5W (S) 10R 5%




TE Part # 2176085-7
EP 9W (S) 100R 5%




TE Part # 2176084-7
EP 7W (S) 100R 5%



TE Part # 1-2176083-1
EP 5W (S) 470R 5%



TE Part # 2176079-5
EP 3W 47R 5%




TE Part # 2176081-7
EP 1W (S) 100R 5%

Also in the Series | **Neohm EP**




[Through-Hole Resistors\(607\)](#)


Customers Also Bought



TE Part #5177985-3
0.8FH,R05H.5,080,08/Sn,TR,SC




TE Part #5406903-1
MJ,RJ11,SMT,1X2,6/6,GRAY,22"RL



TE Part #825433-4
MOD 2 PINHDR 1X4 P.



TE Part #4-2112594-1
4(6)POS,NANOMQS,REC HSG,ASSY, SEALED




TE Part #154718-7
PL 250 REC TERMINAL 18-14 AWG PTPPB




TE Part #825433-7
MOD 2 PINHDR 1X7 P.



TE Part #2176327-8
CRGP 0805 39R 1%



TE Part #354055-E
SMCB 16 F AB VV 7-13 CL * H007 137 E002



TE Part #4623554001
[CGPT-32/16-0-SP](#)



TE Part #3-1462000-1
[C93416=MT Relay 200 mW 5 V](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2176045-2_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176045-2_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176045-2_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wirewound Anti Surge Resistors - Type EP Series

English