



**Part Number :** [1512072411](#)  
**Product Description :** CP-6.5 Receptacle Housing,  
Glow-Wire Capable, 6.50mm Pitch, Dual Row, 4  
Circuits, Natural  
**Series Number :** 151207  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

- [1512072411\\_sd.pdf](#)
- [1512070001-PK-000.pdf](#)

### 3D Models and Design Files


- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

### Specifications

- [PS-151048-0001-001.pdf](#)
- [2034380001-PS-000.pdf](#)
- [2035550001-PS-000.pdf](#)
- [1512070001-TS-000.pdf](#)
- [2034380001-TS-000.pdf](#)
- [2035550001-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Connector Housings
Series	151207
Description	CP-6.5 Receptacle Housing, Glow-Wire Capable, 6.50mm Pitch, Dual Row, 4 Circuits, Natural
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	CP-6.5
UPC	191128439800

**Agency**

CSA	LR19980
UL	E29179

## Physical

Circuits (maximum)	4
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.855/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
CP-6.5 Header, 6.50mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Tray Packaging, Glow-Wire Capable, 4 Circuits, Natural (White)	<u><a href="#">1510481411</a></u>
CP-6.5 Plug Housing, 6.50mm Pitch, Dual Row, 4 Circuits, Natural, Glow-Wire Capable	<u><a href="#">2034382411</a></u>
CP-6.5 Header, 6.50mm Pitch, Dual Row, Right-Angle, Polarized, Through Hole, Tube Packaging, 4 Circuits, Natural	<u><a href="#">2035551214</a></u>
CP-6.5 Header, 6.50mm Pitch, Dual	<u><a href="#">2035551224</a></u>

Row, Right-Angle, Polarized, Through Hole, Tape and Reel Packaging, 4 Circuits, Natural	
CP-6.5 Header, 6.50mm Pitch, Dual Row, Right-Angle, Polarized, Surface Mount, Tray Packaging, 4 Circuits, Natural	<u>2035552214</u>
CP-6.5 Header, 6.50mm Pitch, Dual Row, Right-Angle, Polarized, Surface Mount, Tape and Reel Packaging, 4 Circuits, Natural	<u>2035552224</u>

#### Use with Part(s)

Description	Part Number
CP-6.5 Terminal Position Assurance (TPA) Retainer, 2 Circuits	<u>511430205</u>
CP-6.5 Female Crimp Terminals	<u>50597</u>
CP-6.5 Female Crimp Terminals	<u>50598</u>