



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Insert for Contacts**

Contact Type: **Receptacle**

Termination Method to Wire & Cable: **Crimp**

Number of Positions: **32**

Sealable: **No**

Features

Body Features

Primary Product Color	Gray
-----------------------	------

Packaging Features

Packaging Method	Box
Packaging Quantity	10

Product Type Features

Rectangular Connector Insert Type	Insert for Contacts
Sealable	No

Contact Features

Contact Type	Receptacle
Contact Current Rating (Max)	2.2 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Configuration Features

Number of Positions	32
---------------------	----



Dimensions

Wire Size	.08 – .37 mm²
-----------	---------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2080322101-000
HQ-D-032-M

TE Part # CAT-LS0-H3
HDC H3A TIC-LOQ Hood and
Housing: Standard, Cross Mating
Version

Customers Also Bought

TE Part #1939850-1
ME 67M D1100 24P RX ASSY BLACK

TE Part #2316663-2
HD1 TAB CONTACT AU0.38 M SIZE

TE Part #3-178129-6
DYNAMIC 3200 REC HSG 6P DBL

TE Part #T0931006527-000
CODING-PIN-M3-LTF

TE Part #1939847-1
ME 67M PLUG CASE ASSY

TE Part #2-1318119-4
DYNAMIC D2100 REC HSG 8P DBL Y

TE Part #T2120865101-000
HK-HDW3/1/1-23/16/47-M

TE Part #T1509034500-000
H3A-MAG-TL FOR CROSS MATING

TE Part #T3209201122-001
HSK-M20B

TE Part #T3209201102-001
HSK-M20B-D

Documents

Product Drawings

HQ-D-032-F

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2080322201-000_1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_T2080322201-000_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2080322201-000_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

[UL](#)

English

[UL](#)

English