



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual
--------------------	-------------

Physical

Cable length	1.22 m
Colour	Black
Depth	33.6 cm
Height	21.5 cm
Net weight	12 kg
Width	13 cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	Schuko CEE 7/7P
Input voltage limits	150...280 V
Maximum input current	6 A
Switching current capacity	10 A
Input protection type	3-pole circuit breaker
Input voltage	230 V

Output

Rated power in W	700 W
Maximum configurable power in W	700 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised

UPS type	Line interactive
Wave type	Stepped approximation to a sinewave
Nb of power socket outlets	4 Schuko CEE 7
Output voltage	230 V

Conformance

Product certifications	CE
------------------------	----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage altitude	0.00...9144.00 m
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 h
Liquid value	0

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	273 J
Data line protection	RJ11 modem/fax protection

Packing Units

Package 1 Weight	12.94 kg
Package 1 Height	29.5 cm
Package 1 width	24.5 cm
Package 1 Length	44 cm
SCC14	10731304315930

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------