

SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/in/products/1438037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, angled, M12-SPEEDCON, coding: A, Rear mounting, M12 x 1, Solder pins, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239690

Commercial data

Item number	1438037
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ABQ
Product key	ABQEGA
Catalog page	Page 189 (C-2-2013)
GTIN	4046356457514
Weight per piece (including packing)	12.81 g
Weight per piece (excluding packing)	12.2 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/in/products/1438037>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting M12 x 1 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Pin

Connector

Connection 1

Head design	Pin
-------------	-----

SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/in/products/1438037>

Head cable outlet	angled
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting

1438037

<https://www.phoenixcontact.com/in/products/1438037>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037
<https://www.phoenixcontact.com/in/products/1438037>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1438037>

	UL Recognized Approval ID: E118976-20100522			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	22	-

SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037
<https://www.phoenixcontact.com/in/products/1438037>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/in/products/1438037>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	088a9d62-9be1-4326-974d-682bf931b685

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in