

Product data sheet

Specifications



Repacked, push-button, Acti9 iPB, 1NO, grey

A9E18032W



This repacked option saves 0.267 over the standard condition

Main

range of product	Acti9
Product name	Acti9 iPB
Product or component type	Push-button
Device short name	iPB
Standards	IEC 60947-5-1 IEC 60669-1

Complementary

Contacts type and composition	1 NO
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	1 push-button grey
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: Clario Upside: Librio Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71 mm
Colour	White
Electrical durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal1 cable(s) 0.5 mm² rigid Staggered tunnel terminal1 cable(s) 0.5 mm² flexible Staggered tunnel terminal1 cable(s) 0.5 mm² flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm² rigid Staggered tunnel terminal2 cable(s) 2.5 mm² flexible Staggered tunnel terminal2 cable(s) 2.5 mm² flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for storage	-40...80 °C
-------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	42.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.196 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

C6de3800-7220-4403-a6a2-26e1f05e3f4b

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins