



2 YEARS
MANUFACTURER
GUARANTEE

**250
+70
LUMEN**

**3/6h
MAX.**

360°

USB RECHARGEABLE

0,6m

Product number
EAN

1175430020
4007123691234

TECHNICAL DATA

Luminous flux	250 lm	Number of batteries	1
Total luminous flux secondary source	70 lm	Battery type	Built-in battery pack
Colour temperature	5700 K	Battery technology	Lithium-ion
Battery capacity	1 Ah	Impact strength	IK07
Battery voltage	3.7 V	Protection class	III
Light duration max.	6 h	Degree of protection (IP)	IP20
Battery charging time approx.	2 h	Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.26 kg
Weight of product (without packaging)	0.13 kg	Dimension LxWxH (incl. packing)	8.7 cm x 6.2 cm x 27.8 cm
Dimension LxWxH (without packing)	3 cm x 4.7 cm x 18.6 cm		