

Electronic LED flush-mounted dimmer T37.08 - complete device

Item-no.: 3760x0800



Suitable for dimmable LED-lamps, dimmable LED-driver, incandescent- and HV-halogen lamps

Electronic, transistor operated dimmer without inductor

EHMANN Silent Technology - Operates absolutely silent

Optimization possibilities for flicker-free dimming of LED-lamps in min. and max. area

No stand-by consumption because of a real on/off switch

Electronically controlled short-circuit, overload and over-temperature protection with automatic reactivation

Single cover with rotary knob / colour: white (similar to RAL 9010)

Dimmer compatible with common switch ranges from GIRA, Busch Jäger, Berker, Jung etc.

EHMANN Advantage - 100 % quality assurance, 5 years warranty, German manufacturer

EHMANN Service - Adapter inclusive, LED lamp recommendation













Electronic LED flush-mounted dimmer T37.08 - Complete device

Technical data

3 - 35 W LED rated power 5 - 100 W/VA Rated power 230 V ~ (+/- 10%) / 50 Hz Rated voltage

Suitable for dimmable LED-lamps, dimmable LED-driver, incandescent- and HV-halogen lamps

Operating principle: Leading edge

Function: rotation dimmer with pressure two-way switch

Shaft: metal shaft \emptyset 4 mm with fine raster (\emptyset 6 mm with shaft adapter)

Connection: screw terminals up to 2 x 2.5 mm² (rigid)

Temperature protection: resettable thermal switch

Overload/short-circuit protection: electronic

















Red adapter

Allows the use of common covers e.g. Gira, Busch-Jäger, Jung, Berker



LED lamp recommendation

"Which LED lamp works ideal with this dimmer"



Tuning possibility for flickerfree dimming of LED-lamps

In case of flickering during dimming the LED lamp, you can try to adjust in the lowest and highest dimming range the minimum and maximum brightness to optimize the dimming behavior.





Item-no. 3760x0800

EAN 401209600673 2

PU 10

84 x 84 x 54 mm Dimension (L x W x H)