





**Part Number :** 5054730810  
**Product Description :** SlimStack Board-to-Board Receptacle, 0.40mm Pitch, Battery Series, 0.60mm Mated Height, 2.00mm Mated Width, 8 Circuits, 10.0A  
**Series Number :** 505473  
**Status :** Not Recommended For New Design  
**Product Category :** Board-to-Board Connectors



## Documents & Resources

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

## General

Status	Not Recommended For New Design
Category	Board-to-Board Connectors
Series	505473
Description	SlimStack Board-to-Board Receptacle, 0.40mm Pitch, Battery Series, 0.60mm Mated Height, 2.00mm Mated Width, 8 Circuits, 10.0A
Series Name	10A, Battery
Application	Board-to-Board
Comments	10A of current per circuit is applicable if the circuit is constructed by two power pins via a PWB/FPC circuit
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	889056268875

## Electrical

Current - Maximum per Contact	0.5A, 5.0A*
Voltage - Maximum	50V AC (RMS)/DC

## Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.60mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	9.490/mg

Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Plating min - Mating	0.100μm
Plating min - Termination	0.050μm
Polarized to Mating Part	No
Polarized to PCB	No
(p)ower-(s)ignal Configuration	4p - 4s
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount