



IO-Link data splitter

IO-LINK DATA SPLITTER PNP



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Application		
Special feature		Gold-plated contacts
Application		for retrofitting of existing IO-Link systems; for systems without IO-Link capabilities
Electrical data		
Operating voltage		[V] 18...30 DC; (on the master side; on the controller / system: 20...30 DC)
Nominal voltage DC		[V] 24
Current consumption		[mA] < 17; (both sides)
Protection class		III
Reverse polarity protection		yes; (on the master side)
Power-on delay time		[s] < 2; (for communication; response time switching signal: response time device plus IO-Link process cycle time)
Inputs / outputs		
Total number of inputs and outputs		1; (on the controller / system)
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Output signal		switching signal; IO-Link
Electrical design		PNP
Number of digital outputs		1



IO-Link data splitter

IO-LINK DATA SPLITTER PNP

Output function	normally open / normally closed	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	200	
Type of short-circuit protection	pulsed	
Short-circuit proof	yes	
Overload protection	yes	

Interfaces

Communication interface	IO-Link	
Supported DeviceIDs	Type of operation	DeviceID
	IO-Link Device	1107

IO-Link Device		
Note on interfaces	connection to IO-Link masters	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Common - I&D	Identification and Diagnosis
SIO mode	yes	
Required master port type	A	
Min. process cycle time [ms]	4.2	

IO-Link Master		
Note on interfaces	connection to IO-Link devices	
Unterstützte Masterportklasse	A / B	
Transmission type	COM1 (4,8 kBaud); COM2 (38,4 kBaud); COM3 (230,4 kBaud)	
IO-Link revision	1.0; 1.1	
SDCI standard	IEC 61131-9	

Operating conditions

Ambient temperature [°C]	-25...60	
Storage temperature [°C]	-25...70	
Protection	IP 67	

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-4	in plastic or open metal tanks
Shock resistance	DIN EN 60068-2-27	15 g (6 ms)
Vibration resistance	DIN EN 60068-2-6	2 g (10...150 Hz)
MTTF [years]	307	
UL approval	Ta	max. 55 °C
	File number UL	E205959

Mechanical data

Weight [g]	90	
Materials	stainless steel (316L/1.4404); brass (2.0401); PBT; PA; Sealing: FKM;	

E43406



IO-Link data splitter

IO-LINK DATA SPLITTER PNP

Displays / operating elements

Display	switching output	1 x LED, yellow
	operation	1 x LED, green
	IO-Link	1 x LED, yellow

Accessories

Accessory required	Y connection cable 1, EVC843
--------------------	------------------------------


Remarks

Remarks	For information on the maximum cable length please refer to the operating instructions.
	To ensure the function according to technical datasheet and operating instructions the use of the following article is imperative: EVC843
	the device complies with overvoltage category II
Pack quantity	1 pcs.

Electrical connection

Electrical connection - plug


Connector: 1 x M12; coding: A; Contacts: gold-plated



1	L+
2	NC
3	L-
4	C: IO-Link

Electrical connection - socket

Connector: 1 x M12; coding: A; Contacts: gold-plated



1	L+
2	C/Q: IO-Link Master
3	L-
4	OUT1: switching output or IO-Link
5	NC

E43406



IO-Link data splitter

IO-LINK DATA SPLITTER PNP

Electrical connection

Connection

