



Product data sheet

Power tools for trade & industry

Inspection Camera

PRO GIC 12V-5-27 C



High-resolution camera and automatic upright viewing for in-depth inspection and documentation

The most important data

Display size	5 "
Length of camera cable	150 cm
Documentation via	Photo, Video

Part Number 0 601 241 402

Technical data

Technical data

Display size	5 "
Diameter of camera head	8.3 mm
Length of camera cable	150 cm
Field of view (FOV)	75°
Focus distance	30 - 80 mm
Documentation via	Photo, Video
Data Transfer	USB-C®, Micro-SD Card
Dust and splash protection, camera cable	IP 67
Dust and splash protection, tool	IP 54
Max. 30 min immersion for camera cable in	diesel, petrol, engine oil, AdBlue®, ethyl alcohol, salt water (26.5 % salt content)
Weight	0.7 kg



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High resolution of 1280 x 720 pixels ensures clear picture quality on big 5" screen
- The unique AutoUp function enables optimal spatial orientation by automatically turning the image the right way up
- Ideal for tough jobsites thanks to IP-rating for protection against dust and water



PROTECTED TOOLS
Impact | Water | Dust



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

