



Main

Range	New Unica
Product or component type	USB charger
Device presentation	Mechanism with fixing frame
Condition of use	Indoor

Complementary

Device application	Charger
Device mounting	Flush
Number of modules	2 modules
Type of USB power supply	USB type A + C
Colour tint	Anthracite (RAL 7021)
Surface finish	Painted powder coated
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Power consumption in W	0.3 W
Nominal output power	45 W
Service life in hours	30000 h 52.5 W
Socket number	2
Integrated connection type	1 USB type A 5 V DC, maximum load current: 1.5 A 1 USB type C 5 V DC, maximum load current: 3 A
Material	Plastic: housing
Protection type	Short-circuit Surge Overheating Overvoltage Overcurrent
Number of terminals	2 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	2 x 0.75...2 x 2.5 mm ² for rigid cable(s) 2 x 0.75...2 x 2.5 mm ² for flexible cable(s)
Wire stripping length	7 mm
Provided equipment	Fixing frame
Fixing mode	Screws or claws
Ambient air temperature for operation	0...40 °C
Height	71 mm
Width	71 mm
Depth	39 mm
Embedding depth	30 mm
Net weight	0.131 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	1
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Electrical insulation class	Class II
IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information