



Product data sheet

Power tools for trade & industry

Stirring Mechanism

PRO GRW 18V-160



Outstanding design, extraordinary performance: the heavy-duty mixer for all materials

The most important data

Battery voltage	18.0 V
Weight	4.8 kg

Part Number 0 601 1C3 000

Technical data

Technical data

No-load speed, 1st gear	530 rpm
No-load speed	530 / 720 rpm
Weight	4.8 kg
Packaging dimensions (width x length x height)	238 x 405 x 370 mm
Bit holder	M14
Battery voltage	18.0 V
Stirrer basket diameter max	160 mm

Noise/vibration information

Total vibration values

Vibration emission value ah	2 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Splash-free mixing thanks to 3 speed-adjustment options
- Effortless mixing of different materials due to powerful brushless motor with 2 gear stages
- Comfortable ergonomic design with large handle and extension piece for taller users
- Superior mixing performance thanks to constant speed even under higher loads
- Protection ensured with KickBack Control which switches off the tool to reduce the hazard of sudden torque reaction

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

