

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Master cable ring, application: Distributor boxes, number of positions: 11, cable length: 50 m



Commercial data

Item number	1401690
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF3
Product key	AF3ZBX
Catalog page	Page 305 (C-2-2019)
GTIN	4046356569521
Weight per piece (including packing)	5,945 g
Weight per piece (excluding packing)	5,945 g
Customs tariff number	85444995
Country of origin	DE

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Technical data

Product properties

Product type	Cable by the meter
Application	Distributor boxes
Number of positions	11


Electrical properties

Nominal voltage U_N	300 V AC
	300 V DC

Cable/line

Cable length	50 m
--------------	------

PUR halogen-free black [PUR]

Dimensional drawing	
Number of positions	11
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	64x 0.10 mm
AWG signal line	20
Conductor structure, voltage supply	128x 0.10 mm
AWG power supply	17
Conductor cross section	3x 1 mm ² (power line)
	8x 0.5 mm ² (Signal line)
External cable diameter	9.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, gray/pink, red/blue, white/green, brown/green
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Smallest bending radius, fixed installation	94 mm
Smallest bending radius, movable installation	94 mm

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 94 mm, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Classifications

ECLASS

ECLASS-11.0	27060106
ECLASS-12.0	27060106
ECLASS-13.0	27060106

ETIM

ETIM 9.0	EC003250
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

Accessories

WIREFOX-D 13 - Stripping tool

1212162

<https://www.phoenixcontact.com/in/products/1212162>



Stripping tool, for stripping installation lines of \varnothing 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/in/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm- \varnothing , insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/in/products/1401690>

WIREFOX 4 - Stripping tool

1212156

<https://www.phoenixcontact.com/in/products/1212156>



Stripping tool, for cables and conductors (especially for rubber and silicone insulations) from 0.1 - 4 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in