# 19mm Panel Sealed 10 Amp Metal Pushbuttons

These rugged electromechanical pushbuttons are available in stainless steel or zinc alloy housings and come in momentary or maintained action. Lighting options include center spot, or ring illumination. This 19mm size make the H48M ideal for many applications in the transportation, security, food processing and medical markets.

### **APPLICATIONS**

- Outdoor Controls
- Security Equipment
- Medical Equipment
- Food Processing Equipment
- Military Equipment
- Industrial Machinery
- Transportation: Mass-Transit, Lift Trucks

# Series H48M




ACTUAL SIZE

## **KEY FEATURES:**

- Momentary or Maintained Action
- Stainless Steel Housing
- Center Spot or Ring Illumination
- Variety of LED colors
- Electro-Mechanical

- Panel Sealed to IP67
- ROHS Compliant
- 16-4044 & 16-530004 & 16-40443 (UL and CSA Certified): SPDT Form Z, Silver contacts

# **ORDERING INFORMATION:**



# STANDARDS / AGENCY / RATINGS:












# SERIES H48M: 19MM PANEL SEALED 10 AMP PUSHBUTTON

### **PRODUCT DRAWINGS**



# MECHANICAL / ELECTRICAL CHARACTERISTICS:

### Circuit:

SPDT-DB (Form Z)

**Button travel (nominal):** 

0.09 inches (2.3 mm)

**Operating force (nominal):** 

5.2N (520 grams)

**Contact bounce (nominal):** 

1 millisecond

**Panel thickness:** 

0.020" - 0.177" (0.5 - 4.5 mm)

Temperature index:

-40° C to +85° C (momentary)

-40° C to +65° C (maintained)

Torque (max):

10 inch pounds

**LED** operating temperature:

-13° F to +185° F

(-25° C to +85° C)

**Current ratings:** 

10A @ 125/250 VAC (res) 10A @ 28 VDC (ind)

Actuator life (nominal):

500,000 cycles (momentary) 50,000 cycles (maintained)

### **ELECTRO SPECIFICATIONS**

**Dielectric strength:** 

1,000 VAC

Insulation resistance:

 $1 \, \text{G}\Omega$ 

**Contact resistance:** 

50 m $\Omega$  max (initial)

### **LED SPECIFICATIONS**

	LED CODE	LED		CIRCUITRY	Vf(VDC)		lf
		Color 1	Color 2	CINCULIKY	Color 1	Color 2	(mA)
	A	AMBER	_	· ***	1.6~2.0	_	20
	R	RED	_		1.6~2.0	_	20
	Υ	YELLOW	_		1.6~2.0	_	20
	В	BLUE	_		2.8~3.4	_	20
	G	GREEN	_		2.8~3.4	_	20
	W	WHITE	_		2.8~3.4	_	20
	RB	RED	BLUE	Color 2	1.6~2.0	2.8~3.4	20
	RG	RED	GREEN		1.6~2.0	2.8~3.4	20

Notes:

- 1.) Lead Soldering Temperature (4mm form body): 280°C for 5 seconds
- 2.) Head Soldering Temperature (4mm form body) : 280°C for 3 seconds

### Panel Mounting Information

The series H48M mounts easily into panels of minimum 0.020" (0.5 mm) and maximum 0.177" (4.5 mm) thickness. Front panel sealing to IP67 is achieved by a sealing o-ring fitted to the body of the switch before it is inserted into the panel hole cut-out. It is held onto the panel by means of a metal hex nut tightened down to a torque of 10 inch pounds to achieve the correct sealing pressure. The Basic Switch (16-4044 or 16-530004) has to be installed after the pushbutton actuator is firmly secured to

specified torque onto the panel.

