

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

## 1. Name of cell / battery

Power bank GP-32A

## 2. Manufacturer of cell / battery / product

Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

## 3. Test laboratory of cell / battery / product

Name	Pony Testing International Group
Address	3/F. of Building 2, Xinhaoshng Industrial Park, Yonghe Road, Qiaotou, Baoan District, Shenzhen
Phone	+86-755-26050909
Email	cst@ponytest.com
Website	www.ponytest.com

## 4. ID-number and date

Unique test report identification number	MPIRQAIK4894175US	Date of test report	02.08.2021
--	-------------------	---------------------	------------

## DESCRIPTION OF CELL / BATTERY

### 5. Mark the type of cell/battery with an "•"

<input type="radio"/> Lithium ion cell	<input type="radio"/> Lithium metal cell
<input checked="" type="radio"/> Lithium ion battery	<input type="radio"/> Lithium metal battery

### 6. Parameters

	Cell	Battery
Mass in gram (g):		206,04
Lithium ion: Indicate watt-hour rating (Wh):		37
Lithium metal: Indicate lithium metal content in gram (g):		

### 7. Physical description of cell / battery

Li-Polymer Prismatic 1S1P

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



Name of cell/battery (taken from field 1)

Power bank GP-32A

## 8. Model numbers

1700-0148

## TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>
	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>

## 10. Reference to assembled battery testing requirements

	N/A	<div></div>

## 11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto

ST-SG-AC10-11-Rev.7 - UN38.3

## 12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.

13. Place, Date	14. Title, Surname, First name	15. Company stamp and signature
Assamstadt	Testzentrum i.A. Gehring, K.	K. Gehring <small>Digital unterschrieben von K. Gehring Datum: 2021.09.30 12:14:49 +02'00'</small>