


# MBC75 Series

Low Profile

Open Frame Power Supplies

Medical



The MBC75 Series of open frame medical power supplies feature a wide universal AC input range of 85 V – 264 VAC, offering 75 W of output power in a compact footprint, with a variety of isolated single output voltages.

The MBC series is designed and approved to the latest Medical standards (EN/IEC 60601-1), providing 2 x MOPP isolation for Class I & Class II applications.

These power supplies are ideal for medical, telecom, datacom, industrial equipment and other applications.

## Key Features & Benefits

- 3 x 2 x 1 Inch Form Factor
- 75 Watts with Convection Cooling
- Efficiency up to 93%
- -40 to 70°C Operating Temperature
- Dual Fusing
- Thermal Shut-Down Feature
- 2 Million Hours, Telcordia -SR332-Issue 3
- No Load Power < 0.3 W
- Approved to EN/IEC 60601-1
- Suitable for BF Applications
- Class II Option Available
- RoHS Compliant
- CE Marked

## Applications

- Diagnostic
- Drug Pump
- Dialysis
- Home Health Care
- Monitoring
- Portable Equipment



**bel** POWER  
SOLUTIONS &  
PROTECTION  
a bel group

[belfuse.com/power-solutions](http://belfuse.com/power-solutions)

## 1. MODEL SELECTION

| MODEL NUMBER <sup>1</sup>  | DESCRIPTION                    | VOLTAGE | MAX. LOAD CONVECTION | POWER |
|----------------------------|--------------------------------|---------|----------------------|-------|
| MBC75-1T12L<br>MBC75-1012L | Screw Terminal<br>Molex Header | 12 V    | 6.25 A               | 75 W  |
| MBC75-1T15L<br>MBC75-1015L | Screw Terminal<br>Molex Header | 15 V    | 5.00 A               | 75 W  |
| MBC75-1T24L<br>MBC75-1024L | Screw Terminal<br>Molex Header | 24 V    | 3.12 A               | 75 W  |
| MBC75-1T30L<br>MBC75-1030L | Screw Terminal<br>Molex Header | 30 V    | 2.50 A               | 75 W  |
| MBC75-1T48L<br>MBC75-1048L | Screw Terminal<br>Molex Header | 48 V    | 1.56 A               | 75 W  |
| MBC75-1T58L<br>MBC75-1058L | Screw Terminal<br>Molex Header | 58 V    | 1.29 A               | 75 W  |
| COVER-120-XBC <sup>2</sup> | Metal cover kit accessory      |         |                      |       |

<sup>1</sup> Class II version available. Add suffix "-2" at the end of the Model Number

<sup>2</sup> When used in Cover Kit, de-rate output power to 70 % under all operating conditions.

## 2. INPUT SPECIFICATIONS

Specifications are for nominal input voltage, 25°C unless otherwise stated.

| PARAMETER           | DESCRIPTION / CONDITION                                    | SPECIFICATION                       |
|---------------------|------------------------------------------------------------|-------------------------------------|
| Input Voltage       | Universal<br>(Derate from 75 W @ 100 VAC to 65 W @ 85 VAC) | 85 – 264 VAC / 390 VDC <sup>3</sup> |
| Input Frequency     |                                                            | 47 – 63 Hz                          |
| Input Current       | 115 VAC:<br>230 VAC:                                       | 1 A max.<br>0.5 A max.              |
| No Load Power       | Typical                                                    | < 0.3 W                             |
| Inrush Current      | 115 VAC:<br>230 VAC:<br>264 VAC:                           | 25 A<br>45 A<br>75 A                |
| Leakage Current     | Typical (N.A. For Class II Option)<br>Touch Current        | 300 uA<br><100 uA                   |
| Power Factor        | @ Full Load, Active PFC                                    | > 0.95                              |
| Switching Frequency | Typical                                                    | 60 kHz                              |

<sup>3</sup> Functional, not approved.

### 3. OUTPUT SPECIFICATIONS

| PARAMETER                 | DESCRIPTION / CONDITION                                                   | SPECIFICATION        |
|---------------------------|---------------------------------------------------------------------------|----------------------|
| Output Voltage            | Refer to Model selection table                                            | From 12 V to 58 V    |
| Output Power              | Convection cooling                                                        | 75 W                 |
| Efficiency                | 48 V, 58 V:                                                               | 93%                  |
|                           | 24 V, 30 V:                                                               | 91%                  |
|                           | 12 V, 15 V:                                                               | 90%                  |
| Hold-up Time              | Typical                                                                   | >16 ms               |
| Line Regulation           |                                                                           | +/-0.5%              |
| Load Regulation           |                                                                           | +/-1%                |
| Minimum Load              |                                                                           | 0.0 A                |
| Transient Response        | 25% step load change, at 0.1A/uS slew rate,<br>50% duty cycle, 50 Hz = 4% | recovery time < 5 ms |
| Ripple <sup>4</sup>       | For all outputs                                                           | 1.0 % max.           |
| Output Voltage Adjustment |                                                                           | +/-3%                |
| Rise Time                 | Typical                                                                   | 55 ms                |
| Set Point Tolerance       |                                                                           | +/-1%                |
| Over Current Protection   |                                                                           | > 110%               |
| Over Voltage Protection   | Latch type (AC recycling required)                                        | 110 to 140%          |
| Short Circuit Protection  | Hiccup mode                                                               |                      |
| Cooling                   | With natural convection cooling for input 100 – 264 VAC                   | 75 W                 |

<sup>4</sup> Ripple is peak to peak with 20 MHz bandwidth and 10 µF (Electrolytic capacitor) in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.

### 4. EMC SPECIFICATIONS

| PARAMETER                          | DESCRIPTION / CONDITION                                         | SPECIFICATION        |
|------------------------------------|-----------------------------------------------------------------|----------------------|
| Conducted Emissions                | EN 55011-B, CISPR22-B, FCC PART15-B                             | Pass                 |
| Radiated Emissions                 | EN 55011 A;                                                     | Pass                 |
|                                    | with external core (King core K5B RC 25x12x15-M in input cable) | Level B              |
| Input Current Harmonics            | EN 61000-3-2                                                    | Class D              |
| Voltage Fluctuation and Flicker    | EN 61000-3-3                                                    | Pass                 |
| ESD Immunity                       | EN 61000-4-2                                                    | Level 4, Criterion A |
| Radiated Field Immunity            | EN 61000-4-3                                                    | Level 3, Criterion A |
| Electrical Fast Transient Immunity | EN 61000-4-4                                                    | Level 3, Criterion A |
| Surge Immunity                     | EN 61000-4-5                                                    | Level 3, Criterion A |
| Conducted Immunity                 | EN 61000-4-6                                                    | Level 3, Criterion A |
| Magnetic Field Immunity            | EN 61000-4-8                                                    | Level 4, Criterion A |
| Voltage Dips, Interruptions        | EN 61000-4-11                                                   | Criterion B          |


## 5. SAFETY SPECIFICATIONS

| PARAMETER          | DESCRIPTION / CONDITION                                                        | SPECIFICATION |
|--------------------|--------------------------------------------------------------------------------|---------------|
| Isolation Voltage  | Input to Output: (For medical applications)                                    | 4000 VAC      |
|                    | Input to GND: (Not Applicable for Class II Option)                             | 1500 VAC      |
|                    | Output to GND: for type BF                                                     | 1500 VAC      |
|                    | for type B (N/A for Class II Option)                                           | 500 VAC       |
| Protection Level   | Primary to Secondary:                                                          | 2 MOPP        |
|                    | Primary to Earth:                                                              | 1 MOPP        |
|                    | Secondary to Earth:                                                            | 1 MOPP        |
| Safety Standard(s) | EN60601-1, IEC 60601-1 (ed.3), ANSI / AAMI ES 60601 - 1, CSA C22.2 No. 60601-1 |               |
| Agency Approvals   | Nemko, UL, C-UL                                                                |               |
| CE mark            | Complies with LVD Directive                                                    |               |

## 6. ENVIRONMENTAL SPECIFICATIONS

| PARAMETER             | DESCRIPTION / CONDITION                                         | SPECIFICATION      |
|-----------------------|-----------------------------------------------------------------|--------------------|
| Operating Temperature | -40 to 0°C startup guaranteed, with spec deviation <sup>5</sup> | -40 to +70°C       |
| Storage Temperature   |                                                                 | -40 to +85°C       |
| Cooling               | With natural convection cooling at 100 to 264 VAC               | 75 W               |
| Relative Humidity     | Noncondensing                                                   | 5% to 95%          |
| Altitude              | Operating:                                                      | 16,000 ft          |
|                       | Nonoperating:                                                   | 40,000 ft.         |
| Reliability           | MTBF according to Telcordia -SR332-Issue 3                      | 2.00 million hours |

<sup>5</sup> Output ripple can be more than 10% of the output voltage.



Convection load: 75W up to 50°C  
De-rate above 50 °C @ 2.5% per °C




Figure 1. Derating Curves

## 7. CONNECTOR & PIN DESCRIPTION

| CONNECTOR           | PIN | DESCRIPTION / CONDITION |            |                           | MANUFACTURER / PN                                                                              |
|---------------------|-----|-------------------------|------------|---------------------------|------------------------------------------------------------------------------------------------|
| AC Input Connector  | J1  | Pin 1                   | AC Line    | Screw Terminal (Option 1) | Molex: 39357-0003<br>Tyco-2-1776112-3                                                          |
|                     |     | Pin 2                   | Not Fitted |                           | Molex: 1722861103                                                                              |
|                     |     | Pin 3                   | AC Neutral | Molex Header (Option 2)   | (Mating conn: Molex 1722561003,<br>Molex 1722561103,<br>Molex 1722563103)                      |
| DC Output Connector | J2  | Pin 1, 2                | V1 -VE     | Screw Terminal (Option 1) | Molex: 39357-0004<br>Tyco-2-1776112-4                                                          |
|                     |     | Pin 3, 4                | V1 +VE     | Molex Header (Option 2)   | Molex: 1722861104<br>(Mating conn: Molex 1722561004,<br>Molex 1722561104,<br>Molex 1722563104) |

## 8. MECHANICAL SPECIFICATIONS

| PARAMETER  | DESCRIPTION / CONDITION                |
|------------|----------------------------------------|
| Weight     | 180 g max                              |
| Dimensions | 76.2 x 50.8 x 25.4 mm (3 x 2 x 1 inch) |




Figure 2. Mechanical Drawing - Screw Terminal (Option 1)





Figure 3. Mechanical Drawing - Molex Header (Option 2)



MECHANICAL OUTLINE DIMENSIONS  
ALL DIMENSIONS ARE IN MM  
GEN TOLERANCE:  $\pm 1.0$  MM  
MATERIAL: CRCA/GI 1.0MM THICK  
(POWDER COATING/ PASSIVATION/  
ED COATING BLACK)

Figure 4 - Mechanical Drawing - With Cover Kit

**NOTES:** In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- 1 Stand off, used to mount PCB has OD of 5.4 mm max.
- 2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3 Washer, if used, to have dia of 6.5 mm max.

**For more information on these products consult: [tech.support@psbel.com](mailto:tech.support@psbel.com)**

**NUCLEAR AND MEDICAL APPLICATIONS** - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

**TECHNICAL REVISIONS** - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.