




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Number of Rows: **1**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	3
Number of Loaded Positions	3
Number of Power Positions	3
PCB Mount Orientation	Vertical
Number of Positions	3
Number of Rows	1



Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 μm[50 μin]
Contact Mating Area Plating Material Thickness	2.032 μm[80 μin]
Contact Layout	Inline
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Pin
Contact Current Rating (Max)	4.2 A

Termination Features

Termination Post & Tail Length	3.4 mm[.134 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention Type	Kinked Legs
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Width	6.4 mm[.25 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]



Connector Height	8.8 mm[.346 in]
Connector Length	10 mm[.393 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	600
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability











Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 <p>TE Part # 1969729-9 EP2.5 Shrouded HDR ASSY 9P VERT w /o boss</p>	 <p>TE Part # 1-1969729-0 EP2.5 Shrouded HDR ASSY 10P VERT w/o boss</p>	 <p>TE Part # 1969729-7 EP2.5 Shrouded HDR ASSY 7P VERT w /o boss</p>	 <p>TE Part # 1-1969730-0 EP2.5 SHROUDED HDR ASSY 10P VERTICAL</p>
 <p>TE Part # 1744439-3 EP2.5 Shrd HDR ASSY 3P VERT, GW</p>	 <p>TE Part # 1969729-4 EP2.5 Shrouded HDR ASSY 4P VERT w /o boss</p>	 <p>TE Part # 2132415-3 EP2.5 Shrouded HDR ASSY 3P VERT w /o boss</p>	 <p>TE Part # 1969729-5 EP2.5 Shrouded HDR ASSY 5P VERT w /o boss</p>
 <p>TE Part # 1969729-2 EP2.5 Shrouded HDR ASSY 2P VERT w /o boss</p>	 <p>TE Part # 1-2132415-5 EP2.5 Shrouded HDR ASSY 15P VERT w/o boss</p>		

Also in the Series | Economy Power 2.5

 <p>Connector Contacts(6)</p>	 <p>Connector Hardware(49)</p>	 <p>PCB Headers &amp; Receptacles(533)</p>	 <p>Rectangular Power Connectors(531)</p>
--	--	---	--



Wire-to-Board Connector Assemblies & Housings(305)




Wire-to-Board Headers & Receptacles (533)

Customers Also Bought



TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



TE Part #281934-2  
SINGLE WIRE SEAL



TE Part #114017-ZZ  
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part #DT04-2P  
REC, 2P, GRY, N



TE Part #DT06-2S  
PLG, 2P, GRY, N



TE Part #CAT-D487-W416  
Wedgelocks: DEUTSCH DT

Documents

Product Drawings

EP2.5 Shrouded HDR ASSY 3P VERT w/o boss

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1969729-3\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1969729-3\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1969729-3\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English