Product datasheet

Specifications



Discontinued

photo-electric sensor - XUB - emitter - laser - 12..24VDC - cable 2m

XUBLBKCNL2T

Discontinued on: 01 November 2020

XUBLBKCNL2T has not been replaced. Please contact your customer care centre for more information.

Main

Range of product	Telemecanique Photoelectric sensors XU
Series name	Application material handling
Electronic sensor type	Photo-electric sensor transmitter
Sensor name	XUB
Sensor design	Cylindrical M18
Detection system	Thru beam
Material	Metal
Supply circuit type	DC
Wiring technique	3-wire
Electrical connection	Cable
Cable length	2 m
Product specific application	-
Emission	Red laser thru beam class 1 670 nm conforming to IEC 60825-1
[Sn] nominal sensing distance	0…100 m thru beam need a receiver

Complementary

Enclosure material	Nickel plated brass
Lens material	PMMA
Add on input	Test by emission breaking
Wire insulation material	PvR
Status LED	1 LED (green) for supply on
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10…30 V DC
Switching capacity in mA	<= 100 mA (overload and short-circuit protection)
Switching frequency	<= 1500 Hz
Maximum voltage drop	<1.5 V (closed state)
Current consumption	25 mA no-load
Maximum delay first up	80 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum delay response	0.4 ms
Maximum delay recovery	0.4 ms
Diameter	18 mm
Length	52 mm
Net weight	0.11 kg

Environment

Product certifications	CSA CE UL
Ambient air temperature for operation	-10…45 °C
Ambient air temperature for storage	-40…70 °C
Vibration resistance	7 gn, amplitude = +/- 1.5 mm (f = 10…55 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP67 double insulation conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	111.0 g
Package 1 Height	3.6 cm
Package 1 width	7 cm
Package 1 Length	13 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Contractual warranty

Warranty	18 months

Product datasheet XUBLBKCNL2T


Dimensions Drawings

Dimensions



Mounting

Adjustment




(1) Adjust the focusing point of the laser beam by rotating the serrated sleeve
(2) Located on the face of the sensor. Re-tighten fixing screws

Product datasheet XUBLBKCNL2T

Connections and Schema

Wiring Schemes

Transmitter




(+) BN : Brown
(-) BU : Blue
Input 2/VI: Not connected: beam made, connected to (-): beam broken

Product datasheet XUBLBKCNL2T


Performance Curves

Curves

Detection Curve (Set to Infinity)




Excess Gain Curve




(X) Distance (m)
(Y) Gain

Standard Curve



(X) Distance focusing point (m)
(Y) Minimum size of the object to be detected (mm)

Detection Limit Curve



(X) Distance focusing point (m)
(Y) Minimum size of the object to be detected (mm)