

CUT RESISTANT WITH OUTSTANDING OILY GRIP

Cut resistant glove with Zorb-It[®] technology which provides outstanding grip in oily conditions due to an extra absorbent sponge nitrile coating.

FEATURES

- > Cut resistant: Level D (EN 388:2016)
- Liner is reinforced with Kevlar® for improved cut resistance
- > Kevlar[®] liner is inherently flame resistant
- Lightweight, 15 gauge breathable liner allows warm air and moisture from inside to escape, keeping hands dry and comfortable
- Zorb-It[®] sponge nitrile palm absorbs oil and grease to increase grip and durability in oily environments
- Manufactured using SHOWA's patented hand former design for a comfortable fit and to minimise hand fatigue
- > Seamless knitted liner prevents irritation
- Suitable for contact heat resistance up to 250°C (approx. 15 seconds)





SUITABLE FOR

Typical Industries

- Automotive
- Construction
- Glass and Glazing
- Logistics
- Mechanical
- Metallurgy

Suitable Applications

- Automotive Assembly
- Goods Handling
- Handling Components with Sharp Edges
- Handling Oily Components
- Maintenance

CERTIFICATION







X2XXXX

See overleaf for explanation

4X32D





sн<u>с</u>ша. **4561**

PRODUCT INFORMATION

	MATERIALS	LINER:	13 gauge Kevlar [®] , spandex
		COATING:	Sponge nitrile
	COLOUR	Yellow/black	
	LENGTH (mm)	250 (size dependent)	
	CUFF STYLE	'LE Elasticated knit wrist	

ORDERING DETAILS


SIZE	CODE	PACKAGING
6/S 7/M 8/L 9/XL 10/XXL	SHO45611 SHO45612 SHO45613 SHO45614 SHO45615	12 pairs per bag 72 pairs per case

RECOMMENDATIONS FOR USE

- USE: Cut resistant glove. Not suitable for thermal (above 250 C), electrical and Chemical protection. Do not use near moving machines if there is a risk of entanglement
- STORAGE : Store in dry conditions in the original packaging and away from direct sunlight
- CLEANING: To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- LIFETIME: Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

CERTIFICATION LEGENDS

L-



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



HEAT AND FIRE EN 407

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4 0-4 Resistance to Large Splashes of Molten Metal Resistance to Small Drops Of Molten Metal Radiant Heat Resistance Convective Heat Resistance Contact Heat Resistance Burning Behaviour

EUROPE

www.globusgroup.com

- E: sales@globus.co.uk
- T: +44 (0)161 877 4747
- F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

- E: gcc@globusgroup.com
- **T:** +971 4 882 9962
- F: +971 4 882 9963

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES



©2020 Globus (Shetland) Ltd | SHO-DATA-4561_0620

EU compliance certificate delivered by the notified body SGS Fimko Oy, Särkiniementie 3, Helsinki, 00211, Finland (Notified Body number 0598)

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary