


FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers robust protection against environmental factors
- **4 Cores:** Supports multiple connections and applications
- **Temperature Range -15 °C to 70 °C:** Suitable for diverse operating conditions
- **Voltage Rating of 500 V:** Ensures compatibility with high-voltage systems
- **Plain Conductor Type:** Simplifies installation and maintenance
- **White Jacket Colour:** Enhances visibility and identification

RS PRO 0.75 mm² Flexible Cable, 50 m

RS Stock No: 606-152



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for a variety of electrical applications requiring reliable and efficient power transmission. With a length of 50 metres, it is ideal for installations where flexibility and durability are essential. The cable's annealed copper conductor ensures excellent conductivity, making it suitable for both residential and industrial environments.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	50 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	4
Outside Diameter	8.3 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------