



Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**
Connector System: **Wire-to-Board, Wire-to-Device, Wire-to-Wire**
Number of Positions: **2**
Centerline (Pitch): **5 mm [.197 in]**
Sealable: **Yes**

Features

Product Type Features

Connector & Housing Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V

Body Features

Cable Exit Angle	180°
Body Material	PBT GF
Primary Product Color	Gray
Connector Code	B



Contact Features

Contact Size	1.8mm
--------------	-------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

Dimensions

Product Width	24.05 mm[.947 in]
Product Length	22 mm[.87 in]
Product Height	27.6 mm[1.09 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1800
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------





EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>







Compatible Parts

 TE Part # 184006-1 2 POS. PLUG ASSY, KEY D, GREEN	 TE Part # 184164-1 2 POS. CAP HSG., KEY B	 TE Part # 184060-1 6 POS./6 CIRC PLUG ASSY, KEY A	 TE Part # 184022-1 2 POS. PLUG ASSY, KEY M, BLACK
 TE Part # 184000-1 2 POS. PLUG ASSY, KEY A, BLACK	 TE Part # 184141-1 WIRE SEAL,RUBBER,SENSOR,PURPLE, LIM	 TE Part # 184140-1 WIRE SEAL,RUBBER,SENSOR, ORANGE	 TE Part # CAT-EC7491-T273 ECONOSEAL, RECEPTACLE AND TAB



 TE Part # 171631-2 070 TAB CONT GOLD	 TE Part # 184006-2 2 POS. PLUG ASSY, KEY D, GRAY	 TE Part # 184166-1 2 POS. CAP HSG., KEY D	 TE Part # 184163-1 2 POS. CAP HSG., KEY A
 TE Part # 184207-1 2 POS. PLUG ASSY, KEY J	 TE Part # 184004-1 2 POS. PLUG ASSY, KEY C, BLACK	 TE Part # 184165-1 2 POS. CAP HSG., KEY C	 TE Part # 184175-1 2 POS. CAP LP
 TE Part # 184012-1 2 POS. PLUG ASSY, KEY G, GRAY	 TE Part # 184030-3 RECPT, CONTACT 070, PTPPHBZ	 TE Part # 184030-1 RECPT, CONTACT 070, AUPHBZ	 TE Part # 184288-1 TRW E9DB-14A163-CA

Also in the Series | Sealed Sensor Connector SSC System

 Automotive Connector Caps & Covers (7)	 Automotive Connector Locks & Position Assurance(6)	 Automotive Housings(174)	 Automotive Seals & Cavity Plugs(3)
 Automotive Terminals(8)	 Insertion & Extraction Tools(1)	 Other Automotive Connector Accessories(5)	

Customers Also Bought





TE Part #1452299-1
AMP MCP, UNSEALED CONNECTOR HOUSING




TE Part #2278584-1
MCON, CONNECTOR HOUSING



TE Part #1743354-2
MT-II/JPT SLD 16P CAP HSG



TE Part #2278586-1
67 POS COVER ASSY TYPE180



TE Part #936615-2
HYBRID 42P PLUG COVER HSG



TE Part #2278923-1
COVER

Documents

Product Drawings
2 POS. PLUG ASSY, KEY B, GRAY
English

CAD Files
Customer View Model
ENG_CVM_CVM_184002-1_B.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_184002-1_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_184002-1_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English

Product Environmental Compliance
Product Compliance
English
Product Compliance
English



Instruction Sheets

Instruction Sheet (U.S.)

English

Positioning the Double Lock Plate

English